

CY2410-000 | OCC1C-F-471-NNNQC



OCC1C compact CWDM, 8 channels + 1310 nm port, single demux, 1471 nm starting wavelength, 0.250 mm cable

OBSOLETE

This product was discontinued on: July 25, 2023

Replaced By:

8X4939-000 OCC1C compact CWDM, 8 channels + 1310 nm port, single demux, 1471 nm starting wavelength,
OCC1C-F-471-NNNQC-US26 0.250 mm cable

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	CWDM component
Product Series	OCC1C

General Specifications

Device Type	Component, rectangular
Functionality	Demultiplexing
Technology Type	Free space optics
Application	For use in FOSS closures
Circuits, quantity	1
Distribution Type	8-channel CWDM
Interface, Input	Stub tail
Interface, Output	Stub tail
Multiplexers, quantity	1
Port Type, optional	1310 nm port

Dimensions

Pigtail Length, Input	2.5 m 8.202 ft
Pigtail Length, Output	2.5 m 8.202 ft
Pigtail Diameter	0.25 mm 0.01 in

Optical Specifications

CY2410-000 | OCC1C-F-471-NNNQC

Channel Spacing	20 nm
Starting Wavelength	1471 nm

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

