

# H-4X4-CPUSE-DA

4x4 High Power Hybrid Matrix, 698–2700 MHz



## OBSOLETE

This product was discontinued on: **October 31, 2015**

### Replaced By:

H-4X4-CPUSE-DAI6      Low PIM 4x4 High Power Hybrid Matrix, 555–2700 MHz

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Hybrid matrix

## General Specifications

<b>Device Type</b>	Hybrid
<b>Application</b>	Indoor/Outdoor
<b>Color</b>	Black
<b>Inner Contact Plating</b>	Silver
<b>Interface</b>	7-16 DIN Female
<b>Outer Contact Plating</b>	Trimetal

## Dimensions

<b>Height</b>	32.5 mm   1.28 in
<b>Width</b>	191 mm   7.52 in
<b>Length</b>	191 mm   7.52 in

## Electrical Specifications

<b>3rd Order IMD</b>	-150 dBc
<b>3rd Order IMD Test Method</b>	Two +43 dBm carriers

# H-4X4-CPUSE-DA

---

<b>Return Loss, minimum</b>	20.8 dB
<b>Average Power, maximum</b>	100 W
<b>Coupling</b>	6.1 dB
<b>Coupling Tolerance</b>	±1.0dB
<b>Impedance</b>	50 ohm
<b>Isolation at Frequency Band</b>	25 dB @ 698–2700 MHz
<b>Operating Frequency Band</b>	698 – 2700 MHz
<b>Peak Power, maximum</b>	1 kW
<b>Reflected Power, maximum</b>	100 W
<b>VSWR</b>	1.2

## Environmental Specifications

<b>Operating Temperature</b>	-35 °C to +85 °C (-31 °F to +185 °F)
<b>Relative Humidity</b>	Up to 100%
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP65

## Packaging and Weights

<b>Height, packed</b>	50 mm   1.969 in
<b>Width, packed</b>	210 mm   8.268 in
<b>Length, packed</b>	220 mm   8.661 in
<b>Weight, gross</b>	2.3 kg   5.071 lb
<b>Weight, net</b>	1.8 kg   3.968 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

