

CPCF662

Base Product

VisiPatch® 360 to D8PS 1-pair Patch Cord

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Twisted pair patch cord |
| Product Brand | VisiPatch 360® VisiPatch® |
| Product Series | CPC |
| Ordering Note | Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices |

General Specifications

| | |
|---------------------------------------|---------------------|
| ANSI/TIA Category | 5e |
| Cable Type | U/UTP (unshielded) |
| Conductor Type | Stranded |
| Interface, Connector A | VisiPatch® 360 |
| Interface Feature, connector A | Standard |
| Interface, Connector B | RJ45 plug |
| Interface Feature, connector B | Standard |
| Jacket Color | Dark gray |
| Pairs, quantity | 1 |
| Transmission Standards | IEEE 802.3bt Type 4 |
| Wiring | VisiPatch® 360 |

Dimensions

| | |
|---|-------------------|
| Cable Assembly Length Range (m) | 1 – 30 |
| Cable Assembly Length Range (ft) | 1 – 100 |
| Diameter Over Jacket | 3.56 mm 0.14 in |
| Compatible Conductor Gauge, stranded | 24 AWG |

CPCF662

Wiring Diagram

| | Connector A | Connector B |
|------------|-------------|-------------|
| Position 1 | Blue | |
| Position 2 | Lt. Blue | |
| Position 3 | | |
| Position 4 | | Blue |
| Position 5 | | Lt. Blue |
| Position 6 | | |
| Position 7 | | |
| Position 8 | | |

Electrical Specifications

| | |
|-------------------------------|---------|
| dc Resistance, maximum | 0.3 ohm |
| Safety Voltage Rating | 300 V |

Ordering Tree

CPC - ⁹ ¹⁰ ¹¹ ¹²

Outlet Color

| | |
|---|----------------|
| 0 | Not applicable |
| 1 | Black |
| 2 | Blue |
| 3 | Gray |
| 4 | Green |
| 5 | Ivory |
| 6 | Orange |
| 7 | Red |
| 8 | White |
| 9 | Yellow |
| B | Lilac |

Jacket Color

| | |
|---|--------------|
| 1 | Black |
| 2 | Light blue |
| 3 | Dark gray |
| 4 | Spring green |
| 5 | Ivory |
| 6 | Orange |
| 7 | Red |
| 8 | White |
| 9 | Yellow |
| B | Lilac |
| C | Gray |
| K | Pink |
| L | Violet |
| M | Green |
| Z | Blue |

UOM

| | | |
|----|---|------------|
| 11 | F | Foot |
| | M | Meter |
| | N | Inch |
| | C | Centimeter |

Length

12

Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Material Specifications

| | |
|---------------------------------|-----------------|
| Contact Plating Material | Precious metals |
|---------------------------------|-----------------|

CPCF662

Material Type Copper alloy | Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Retention Force, minimum 133 N | 29.9 lbf

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Non-plenum

Flammability Rating UL 94 V-0

Safety Standard ETL | cETL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

Included Products

| | |
|---------------------------------|--|
| 848202800 1074C DG 1/24 RVAR | – GigaSPEED XL® 1074C Category 5e U/UTP Cable, non-plenum, dark gray jacket, 1 pair count, variable length, reel |
|---------------------------------|--|

848202800 | 1074C DG 1/24 RVAR

GigaSPEED XL® 1074C Category 5e U/UTP Cable, non-plenum, dark gray jacket, 1 pair count, variable length, reel

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Twisted pair cable |
| Product Brand | GigaSPEED XL® |


General Specifications

| | |
|--------------------------------|---|
| Product Number | 1074C |
| ANSI/TIA Category | 5e |
| Cable Component Type | Cordage |
| Cable Type | U/UTP (unshielded) |
| Conductor Type, singles | Stranded |
| Conductors, quantity | 2 |
| Jacket Color | Dark gray |
| Pairs, quantity | 1 |
| Transmission Standards | ANSI/TIA-568.2-D CENELEC EN 50288-3-1 ISO/IEC 11801 Class D |

Dimensions

| | |
|--------------------------------------|---------------------|
| Cable Length, special | Variable length |
| Diameter Over Jacket, nominal | 3.556 mm 0.14 in |
| Jacket Thickness | 0.686 mm 0.027 in |
| Conductor Gauge, singles | 24 AWG |

Cross Section Drawing



Electrical Specifications

| | |
|--|---|
| dc Resistance Unbalance, maximum | 5 % |
| dc Resistance, maximum | 9.38 ohms/100 m 2.859 ohms/100 ft |
| Dielectric Strength, minimum | 1500 Vac 2500 Vdc |
| Mutual Capacitance at Frequency | 5.6 nF/100 m @ 1 kHz |
| Nominal Velocity of Propagation (NVP) | 65 % |
| Operating Frequency, maximum | 250 MHz |
| Operating Voltage, maximum | 80 V |
| Remote Powering | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |
| Safety Voltage Rating | 300 V |

Material Specifications

| | |
|----------------------------|---------------|
| Conductor Material | Tinned copper |
| Insulation Material | Polyolefin |
| Jacket Material | PVC |

Mechanical Specifications

| | |
|---------------------------------|-----------------|
| Pulling Tension, maximum | 2.722 kg 6 lb |
|---------------------------------|-----------------|

Environmental Specifications

| | |
|---------------------------------|-------------------------------------|
| Installation temperature | 0 °C to +60 °C (+32 °F to +140 °F) |
| Operating Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |

848202800 | 1074C DG 1/24 RVAR

Environmental Space Non-plenum

Flame Test Method CM

Packaging and Weights

Cable weight 14.882 kg/km | 10 lb/kft

Packaging Type Reel

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system