

# CPCLLP2

## Base Product



GigaSPEED Xpress® GSXP on 1089 Solid Cordage, Modular Patch Cord

### OBSOLETE

This product was discontinued on: March 1, 2019

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America   |
| <b>Portfolio</b>             | SYSTIMAX®   |
| <b>Product Type</b>          | Twisted pair patch cord   |
| <b>Product Brand</b>         | GigaSPEED Xpress®   |
| <b>Product Series</b>        | CPC   |
| <b>Ordering Note</b>         | Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords   Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices |

## General Specifications

|                                       |  |
|---------------------------------------|--|
| <b>ANSI/TIA Category</b>              | 6  |
| <b>Cable Type</b>                     | U/UTP (unshielded)   |
| <b>Conductor Type</b>                 | Solid  |
| <b>Interface, Connector A</b>         | RJ45 plug  |
| <b>Interface Feature, connector A</b> | Standard   |
| <b>Interface, Connector B</b>         | RJ45 plug  |
| <b>Interface Feature, connector B</b> | Standard   |
| <b>Jacket Color</b>                   | Black   Blue   Dark gray   Light blue   Lilac   Orange   Red   Spring green   White   Yellow |
| <b>Pairs, quantity</b>                | 4  |

# CPCLLP2

**Wiring** T568B

## Dimensions

**Cable Assembly Length Range (m)** 1 – 8  
**Cable Assembly Length Range (ft)** 1 – 25  
**Compatible Conductor Gauge, solid** 24 AWG

## Wiring Diagram

|            | Connector A  | Connector B  |
|------------|--------------|--------------|
| Position 1 | White/Orange | White/Orange |
| Position 2 | Orange       | Orange       |
| Position 3 | Lt. Green    | Lt. Green    |
| Position 4 | Blue         | Blue         |
| Position 5 | Lt. Blue     | Lt. Blue     |
| Position 6 | Green        | Green        |
| Position 7 | Lt. Brown    | Lt. Brown    |
| Position 8 | Brown        | Brown        |

## Electrical Specifications

**dc Resistance, maximum** 0.3 ohm  
**Safety Voltage Rating** 300 V

## Material Specifications

**Contact Plating Material** Precious metals  
**Material Type** Copper alloy | Polycarbonate

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times  
**Plug Retention Force, minimum** 133 N | 29.9 lbf

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

# CPCLLP2

---

|                            |            |
|----------------------------|------------|
| <b>Environmental Space</b> | Non-plenum |
| <b>Flammability Rating</b> | UL 94 V-0  |
| <b>Safety Standard</b>     | ETL   cETL |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |