

S-3-TCPUSE-H-D



Multiband Three-way Reactive High Power Splitter, 380–2700 MHz
(Additional mounting bracket PN:42396A-17 sold separately)

OBSOLETE

This product was discontinued on: **March 30, 2016**

Replaced By:

S-3-TCPUSE-H-DI6

Multiband Three-way Low PIM Reactive High Power Splitter, 340–2700 MHz (Additional mounting bracket PN:42396A-17 sold separately)

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Power splitter

General Specifications

Device Type

Splitter

Application

Indoor/Outdoor

Color

Black

Inner Contact Plating

Silver

Interface

7-16 DIN Female

Outer Contact Plating

Trimetal

Dimensions

Height

29 mm | 1.142 in

Width

64 mm | 2.52 in

Length

297 mm | 11.693 in

Electrical Specifications

3rd Order IMD

-150 dBc

S-3-TCPUSE-H-D

3rd Order IMD Test Method	Two +43 dBm carriers
Return Loss, minimum	19 dB
Average Power, maximum	300 W
Dissipative Loss at Frequency Band	0.2 dB @ 380–2700 MHz
Impedance	50 ohm
Operating Frequency Band	380 – 2700 MHz
Peak Power, maximum	3 kW
Power Rating, Splitting	300 W
Reflected Power, maximum	300 W
Split Loss	4.8 dB
VSWR	1.25

Environmental Specifications

Operating Temperature	-25 °C to +85 °C (-13 °F to +185 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	43 mm 1.693 in
Width, packed	80 mm 3.15 in
Length, packed	310 mm 12.205 in
Volume	1066400 mm ³ 65.076 in ³
Weight, gross	0.76 kg 1.676 lb
Weight, net	0.67 kg 1.477 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

