

T-30-UW-NMI6

Low PIM Termination 30 W Load, 340-6000 MHz



OBSOLETE

Replaced By:

T-30-UW-43-M-I6

Low PIM Termination 30 W Load, 340-6000 MHz

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Termination Load

General Specifications

Device Type

Termination Load

Application

Indoor/Outdoor

Color

Silver

Inner Contact Plating

Silver

Interface

N Male

Outer Contact Plating

Trimetal

Dimensions

Length

167 mm | 6.575 in

Diameter, maximum

54 mm | 2.126 in

Electrical Specifications

3rd Order IMD

-163 dBc

3rd Order IMD Test Method

Two +43 dBm carriers

Average Power, maximum

30 W

Impedance

50 ohm

T-30-UW-NMI6

Operating Frequency Band


340 – 6000 MHz

VSWR at Frequency Band

1.2:1 @ 555–2700 MHz | 1.3:1 @ 2700–6000 MHz | 1.4:1 @ 340–555 MHz

T-30-UW-NMI6

Derating Curve



Environmental Specifications

Operating Temperature	-25 °C to +50 °C (-13 °F to +122 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	65 mm 2.559 in
Width, packed	85 mm 3.346 in
Length, packed	200 mm 7.874 in
Weight, gross	0.84 kg 1.852 lb
Weight, net	0.76 kg 1.676 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

