

ConQuest® Cable in Conduit, 3/4 in, SDR 13.5, terracotta (F1177TSEF)



- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Coaxial cable-in-conduit
Product Brand	ConQuest®
Product Series	11 Series
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Color	Terracotta
Conduit Type	Non-toneable
Wall Type	Smooth

Dimensions

Length	304.8 m 1000 ft
Wall Thickness Designation	SDR 13.5
Nominal Size	3/4 in

Packaging and Weights

Weight, net	229.177 kg/km 154 lb/kft
--------------------	----------------------------

Included Products

CX3199976	–	ConQuest® Empty Conduit, 3/4 in, SDR 13.5, terracotta
075T135 EMPTY DUCT COEX		

CX3199976 | 075T135 EMPTY DUCT COEX



ConQuest® Empty Conduit, 3/4 in, SDR 13.5, terracotta

Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

General Specifications

Color	Terracotta
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	304.8 m 1000 ft
Inner Diameter, nominal	22.2 mm 0.874 in
Outer Diameter, nominal	26.67 mm 1.05 in
Wall Thickness Designation	SDR 13.5
Wall Thickness, minimum	1.981 mm 0.078 in
Nominal Size	3/4 in

Material Specifications

Flexural Modulus, minimum	551.581 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238

CX3199976 | 075T135 EMPTY DUCT COEX

Melt Flow Rate, maximum 0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported 304.8 mm | 12 in

Tensile Property Test Method ASTM D638

Tensile Strength at yield, minimum 20.684 N/mm² | 3000 psi

Pulling Tension, maximum 229.064 kg | 505 lb

Environmental Specifications

Environmental Stress Crack Resistance Failure rate of 10% within 96 hours

Environmental Stress Test Method ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net 165.186 kg/km | 111 lb/kft

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance