



## ConQuest® Empty Conduit, 3/4 in, SDR 13.5, gray, with pull rope

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Empty conduit
<b>Product Brand</b>	ConQuest®
<b>Government Funding</b>	Build America Buy America (BABA) compliant*

## General Specifications

<b>Color</b>	Gray
<b>Conduit Type</b>	Non-toneable
<b>Density Test Method</b>	ASTM D792A
<b>Density, maximum</b>	0.955 g/cm <sup>3</sup>   0.035 lb/in <sup>3</sup>
<b>Density, minimum</b>	0.941 g/cm <sup>3</sup>   0.034 lb/in <sup>3</sup>
<b>Design Standard</b>	ASTM D3350-05
<b>Wall Type</b>	Smooth

## Dimensions

<b>Length</b>	1000 ft   304.8 m
<b>Inner Diameter, nominal</b>	0.874 in   22.2 mm
<b>Outer Diameter, nominal</b>	1.05 in   26.67 mm
<b>Wall Thickness Designation</b>	SDR 13.5
<b>Wall Thickness, minimum</b>	0.078 in   1.981 mm
<b>Nominal Size</b>	3/4 in

## Material Specifications

<b>Flexural Modulus, minimum</b>	80000 psi   551.581 N/mm <sup>2</sup>
<b>Flexural Property Test Method</b>	ASTM D790

# CX3199984 | 075G135PP200ROPE COEX

<b>Hydrostatic Design Basis</b>	Not pressure rated
<b>Hydrostatic Design Test Method</b>	ASTM D2837
<b>Material Type</b>	High density polyethylene (HDPE)   Polypropylene
<b>Melt Flow Rate Test Method</b>	ASTM D1238
<b>Melt Flow Rate, maximum</b>	0.39 g/10 min

## Mechanical Specifications

<b>Minimum Bend Radius, unsupported</b>	12 in   304.8 mm
<b>Tensile Property Test Method</b>	ASTM D638
<b>Tensile Strength at yield, minimum</b>	3000 psi   20.684 N/mm <sup>2</sup>
<b>Breaking Strength</b>	200 lb   90.718 kg
<b>Pull Line Type</b>	Rope
<b>Pulling Tension, maximum</b>	505 lb   229.064 kg

## Environmental Specifications

<b>Environmental Stress Crack Resistance</b>	Failure rate of 10% within 96 hours
<b>Environmental Stress Test Method</b>	ASTM D1693, ESCR Condition B

## Packaging and Weights

<b>Weight, net</b>	111 lb/kft   165.186 kg/km
--------------------	----------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

**Environmental Stress Crack Resistance** ESCR—Environmental Stress Crack Resistance