# 7641792

# QN Female Bulkhead

#### Product Classification


Device connector
Bulkhead
Solder
Gold
QN Female
Trimetal
22.1 mm   0.87 in
47.8 mm   1.882 in
22.1 mm   0.87 in

# Outline Drawing

Page 1 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025



### **Electrical Specifications**

Connector Impedance	50 ohm
dc Test Voltage	2500 V
Inner Contact Resistance, maximum	1.5 m0hm
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 6000 MHz
Outer Contact Resistance, maximum	1.5 m0hm
Peak Power, maximum	10 kW
RF Operating Voltage, maximum (vrms)	707 V

# VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0–6000 MHz	1.2	20.83

### Mechanical Specifications

#### Interface Durability

Interface Durability Method

100 cycles IEC 61169-16:9.5

Page 2 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

7641792

**Mechanical Shock Test Method** 

IEC 60068-2-27

# Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Attenuation, Ambient Temperature	20 °C   68 °F
Average Power, Ambient Temperature	40 °C   104 °F
Average Power, Inner Conductor Temperature	100 °C   212 °F
Climatic Sequence Test Method	IEC 60068-1
Corrosion Test Method	IEC 60068-2-11
Damp Heat Steady State Test Method	IEC 60068-2-3
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6
Packaging and Weights	

Weight, net

35.34 g | 0.078 lb



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025