

# C-6-TCPUSE-D

6 dB, Directional Coupler, 380–2700 MHz



## OBSOLETE

This product was discontinued on: **March 30, 2016**

### Replaced By:

C-6-TCPUSE-D-AI6      6 dB, Low PIM Air Directional Coupler, 340–2700 MHz

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Directional coupler

## General Specifications

<b>Device Type</b>	Coupler
<b>Application</b>	Indoor/Outdoor
<b>Color</b>	Black
<b>Inner Contact Plating</b>	Silver
<b>Interface</b>	7-16 DIN Female
<b>Outer Contact Plating</b>	Trimetal

## Dimensions

<b>Height</b>	36 mm   1.417 in
<b>Width</b>	66 mm   2.598 in
<b>Length</b>	194 mm   7.638 in

## Electrical Specifications

<b>3rd Order IMD</b>	-140 dBc
<b>3rd Order IMD Test Method</b>	Two +43 dBm carriers

# C-6-TCPUSE-D

---

<b>Insertion Loss at Frequency Band</b>	1.7 dB @ 380–2700 MHz
<b>Return Loss, minimum</b>	19 dB
<b>Average Power, maximum</b>	200 W
<b>Coupling</b>	6 dB
<b>Coupling Tolerance</b>	±1.0dB
<b>Impedance</b>	50 ohm
<b>Isolation at Frequency Band</b>	20 dB @ 380–2700 MHz
<b>Operating Frequency Band</b>	380 – 2700 MHz
<b>Peak Power, maximum</b>	1 kW
<b>Reflected Power, maximum</b>	40 W
<b>VSWR</b>	1.25

## Environmental Specifications

<b>Operating Temperature</b>	-25 °C to +85 °C (-13 °F to +185 °F)
<b>Relative Humidity</b>	Up to 100%
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP65

## Packaging and Weights

<b>Height, packed</b>	55 mm   2.165 in
<b>Width, packed</b>	110 mm   4.331 in
<b>Length, packed</b>	200 mm   7.874 in
<b>Volume</b>	1210 cc   73.839 in <sup>3</sup>
<b>Weight, gross</b>	0.95 kg   2.094 lb
<b>Weight, net</b>	0.89 kg   1.962 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

