

PFU-P-E-0-060-01

CommScope-Proprietary and Confidential. Preliminary specifications are for illustrative purposes only and will be updated prior to publication.



PoE Extender(5 Gbps), Universal Mount, Outdoor, 1-Port

- Environmentally sealed and tested
- Electrical power management
- Circuit protection electronics
- Optical to electrical Media Conversion
- Automatically conditions electrical voltage to the correct level
- 1 60W PoE port

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	PoE extender/Media converter

General Specifications

Data Transfer Rate, maximum	5 Gb
Interface, Input	10GBASE-X
Interface, Output	10/100/1000/2.5G/5GBASE-T
Mounting	Universal pole mount Universal wall mount
Total Ports, quantity	3
Transmission Standards	10/100/1000/2.5G/5GBASE-T 10GBASE-X
Input/Output Interface	2 input / 1 output

Dimensions

Height	224.71 mm 8.847 in
Width	283 mm 11.142 in
Depth	77.02 mm 3.032 in

PFU-P-E-O-060-01

Port Configuration

Notes:

- This table provides a partial listing of the maximum supported hybrid cable distances for a range of NEC Class 2 power supply output voltages, hybrid cable copper gauges and extender output power levels.
- NEC Class 2 requires a power supply unit (PSU) limited to less than 60V dc. In practice, some commercial 48V power supplies may be configured to output from 48 V up to about 57 V. P_{out} is the maximum total PoE Extender output power.

PSU Output Voltage	Cable Gauge (AWG)	Max Cable Length (m) Pout = 60W	Max Cable Length (m) Pout = 45W	Max Cable Length (m) Pout = 30W	Max Cable Length (m) Pout = 15.4W	Max Cable Length (m) Pout = 7W
Maximum (57V)	12	888	1301	1886	3131	4633
	16	351	514	746	1238	1833
Nominal (48V)	12	630	922	1335	2217	3280
	16	249	365	528	877	1297
Minimum (40.5V)	12	448	630	900	1494	2211
	16	177	249	356	591	874

Assumptions:

- Hybrid cable ambient temperature: 20 °C (Underground/Ducted)
- CommScope Cat6/6a outdoor patch cord length: 50 m
- Patch cord ambient temperature: 55 °C (Sunlight Exposed)

Electrical Specifications

Input Voltage Range -25 to -57 Vdc

Material Specifications

Finish Powder coated, off-white

Material Type Aluminum

Environmental Specifications

Installation temperature -5 °C to +45 °C (+23 °F to +113 °F)

Operating Temperature -40 °C to +65 °C (-40 °F to +149 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Outdoor

Qualification Standards CISPR 22/FCC CFR 47 | EN300386 | ETSI EN 300 019-1-4 | IEC 60529, IP68 | IEC 60950-1 | IEC 60950-22 | IEC 62368 | IEEE 802.3bt Type 3 | NEC Class 2

Safety Standard CE | CSA | FCC | RCM | SELV | WEEE

PFU-P-E-O-060-01

Packaging and Weights

Weight, net 5.08 kg | 11.199 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

