

9905-41



Black 3/4 in PVC Tape, 66 ft

Product Classification

Product Type	Weatherproofing tape
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Application	Provides additional moisture seal for cable connections
Applications per Kit	Four 1/2 in-1/2 in Four 1/2 in-7/8 in to device One 1/2 in-2-1/4 in Two 1/2 in-7/8 in
Color	Black

Dimensions

Width	19.05 mm 0.75 in
Length	20,116.801 mm 792 in
Nominal Size	1-1/4 in 1-5/8 in 1/2 in 1/4 in 2-1/4 in 3/8 in 5/8 in 7/8 in

Material Specifications

Material Type	PVC tape
----------------------	----------

Environmental Specifications

Operating Temperature	-10 °C to +80 °C (+14 °F to +176 °F)
UV Resistance Test Method	PVC tape test method UL 510, ASTM D1000
Weather Resistance Test Method	04AS00-03.6.0 MIL-STD-1344A, Method 1002

Packaging and Weights

Height, packed	60.96 mm 2.4 in
Width, packed	60.96 mm 2.4 in
Length, packed	20.32 mm 0.8 in

9905-41

Packaging quantity 1
Weight, gross 0.11 kg | 0.243 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system