

SFX-ADMR



7-16 DIN Male Right Angle for 1/2 in SFX-500 cable

OBSOLETE

This product was discontinued on: December 2, 2015

Product Classification

Product Type Wireless and radiating connector

General Specifications

Body Style Right angle
Cable Family SFX-500
Inner Contact Attachment Method Captivated
Inner Contact Plating Silver
Interface 7-16 DIN Male
Mounting Angle Right angle
Outer Contact Attachment Method Radial compression
Outer Contact Plating Silver
Pressurizable No

Dimensions

Height 48.26 mm | 1.9 in
Length 53.34 mm | 2.1 in
Diameter 36.07 mm | 1.42 in
Nominal Size 1/2 in

Electrical Specifications

3rd Order IMD at Frequency -115 dBm @ 1800 MHz
3rd Order IMD Test Method Two +43 dBm carriers
Return Loss Note Measurements taken using a .9 m (3 ft) jumper assembly

SFX-ADMR

Average Power at Frequency	870.0 W @ 900 MHz
Cable Impedance	50 ohm
Connector Impedance	50 ohm
dc Test Voltage	2500 V
Inner Contact Resistance, maximum	1 mOhm
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 6000 MHz
Outer Contact Resistance, maximum	0.4 mOhm
Peak Power, maximum	15.6 kW
RF Operating Voltage, maximum (vrms)	707 V
Shielding Effectiveness	110 dB

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0.05–1.0 GHz	1.052	31.92
1.0–2.0 GHz	1.08	28.3
2.0–2.5 GHz	1.1	26.45
2.5–5.0 GHz	1.433	14.99
5.0–6.0 GHz	1.79	11

Mechanical Specifications

Connector Retention Tensile Force	889.64 N 200 lbf
Connector Retention Torque	1.4 N-m 12.356 in lb
Coupling Nut Proof Torque	50 N-m 442.537 in lb
Coupling Nut Proof Torque Method	IEC 61169-4:9.3.6
Insertion Force	199.99 N 44.96 lbf
Insertion Force Method	IEC 61169-4:15.2.4
Interface Durability	500 cycles
Interface Durability Method	IEC 61169-4:17
Mechanical Shock Test Method	IEC 60068-2-27

Environmental Specifications

Operating Temperature	-57 °C to +85 °C (-70.6 °F to +185 °F)
------------------------------	--

SFX-ADMR

Storage Temperature	-70 °C to +100 °C (-94 °F to +212 °F)
Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F
Average Power, Inner Conductor Temperature	100 °C 212 °F
Corrosion Test Method	IEC 60068-2-11
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6

Packaging and Weights

Weight, net	206 g 0.454 lb
--------------------	------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Immersion Depth	Immersion at specified depth for 24 hours
------------------------	---