

Standard Grounding Kit for 1/4 in and 3/8 in corrugated coaxial cable and elliptical waveguide 240 and 380

Product Classification

Product TypeGrounding kitProduct BrandHELIAX®

Ordering Note ANDREW® standard product (Global)

General Specifications

Bonding Conductor Jacketing MaterialPVCBonding Conductor MaterialCopperBonding Conductor Wire Size6 gauge

Cable Type Corrugated | Elliptical waveguide

Color Black

Grounding Kit Type Standard Grounding Kits

Grounding Strap Material Copper

Lug Attachment Factory attached

Lug Type Two-hole lug

Thread Size 3/8 in

Dimensions

Bonding Conductor Length609.6 mm| 24 inCable Jacketing Removal Length, maximum58.42 mm| 2.3 inCable Jacketing Removal Length, minimum55.88 mm| 2.2 inCompatible Diameter, maximum9.652 mm| 0.38 inCompatible Diameter, minimum6.223 mm| 0.245 in

Nominal Size 1/4 in | 3/8 in

Waveguide Size WR28 | WG22 | R320 | WR42 | WG20 | R220

ANDREW® an Amphenol company

Electrical Specifications

Current Handling Tested to withstand 100,000 amps peak current surge

Current Handling Test Method MIL-STD-1757

Grounding, Bonding and Shielding Test Method MIL-STD-188-124A

Lightning Protection Test MethodIEC 1024-1

Material Specifications

Rivet Material Copper

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)Storage Temperature $-40 \,^{\circ}\text{C}$ to $+80 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

Blowing Rain Test MethodMIL-STD-810, Method 506Corrosion Test MethodMIL-STD-1344, Method 1001Freezing Rain/Icing Test MethodMIL-STD-810, Method 521Humidity Test MethodMIL-STD-1344, Method 1002

Immersion Test MethodIEC 60529:2001, IP68UV Resistance Test MethodMIL-STD-810, Method 505Vibration Test MethodMIL-STD-202, Method 214Weatherproofing MethodButyl and electric tape

Packaging and Weights

 Height, packed
 254 mm | 10 in

 Width, packed
 152.4 mm | 6 in

 Length, packed
 50.8 mm | 2 in

Included Grounding kit | Hardware | Lug | One roll of 2-1/2 in butyl rubber

tape | One roll of 3/4 in PVC tape

Packaging quantity 1

Weight, gross 0.26 kg | 0.573 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value



ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

42615-10 - Butyl Rubber Tape, 24 in 9905-71 - Black 2 in PVC Tape, 20 ft

* Footnotes

Grounding, Bonding and Shielding Test Method Military Standard for Grounding, Bonding, and Shielding: Bond Resistance

Requirement of a Maximum dc resistance of 0.001 ohm

Lightning Protection Test MethodProtection Against Lightning Electromagnetic Impulse, Table 1—Protection

Level III-IV, 1995-02





Butyl Rubber Tape, 24 in

Product Classification

Product Type Weatherproofing tape

Product Brand HELIAX®

Ordering Note ANDREW® non-standard product

General Specifications

Application Provides additional moisture seal for cable connections

Applications per Kit One 1/2 in-2-1/4 in | One 1/2 in-7/8 in | One 1/2 in-7/8 in to

device | Two 1/2 in-1/2 in

Color Black

Dimensions

 Width
 63.5 mm | 2.5 in

 Length
 609.6 mm | 24 in

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7

/8 in

Material Specifications

Material Type Butyl rubber tape

Environmental Specifications

Operating Temperature $-55 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-67 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

UV Resistance Test Method

Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4

hours of condensation at 104 °F

UV Resistance, minimum with no degradation ≥1000 hours

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packaging and Weights

Height, packed 63.5 mm | 2.5 in

ANDREW® an Amphenol company

Width, packed 71.12 mm | 2.8 in

Length, packed 25.4 mm | 1 in

Packaging quantity

Weight, gross 0.17 kg | 0.375 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system





Black 2 in PVC Tape, 20 ft

Product Classification

Product Type Weatherproofing tape

Product Brand HELIAX®

Ordering Note ANDREW® non-standard product

General Specifications

Application Provides additional moisture seal for cable connections

Applications per Kit Four 1/2 in -1/2 in | Four 1/2 in -7/8 in to device | One 1/2 in -2-1/4 in | Two 1/2 in -7/8

in

Color Black

Dimensions

 Width
 50.8 mm | 2 in

 Length
 6096 mm | 240 in

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7/8 in

Material Specifications

Material Type PVC tape

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +80 \,^{\circ}\text{C} \ (+14 \,^{\circ}\text{F to } +176 \,^{\circ}\text{F})$

UV Resistance Test Method PVC tape test method UL 510, ASTM D1000

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packaging and Weights

 Height, packed
 63.5 mm | 2.5 in

 Width, packed
 63.5 mm | 2.5 in

 Length, packed
 50.8 mm | 2 in



Packaging quantity

Weight, gross 0.08 kg | 0.176 lb

1

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

