



CWST wraparound repair sleeve heat shrink kit, unpressurized, for 8 to 43 mm cable diameter, 1500 mm long

- Excellent split resistance of the composite structure offers superior resistance to mechanical abuse during and after the installation
- Integrated moisture barrier completely reconstitutes the cable sheath construction

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Heat shrink repair sleeve
Product Series	CWST

General Specifications

Color	Black
Sealant Type	Hotmelt adhesive

Dimensions

Length	1500 mm 59.055 in
Expanded Inside Diameter, minimum	43 mm 1.693 in
Recovered Inside Diameter, maximum	8 mm 0.315 in
Single Cable Diameter, maximum	43 mm 1.693 in
Single Cable Diameter, minimum	8 mm 0.315 in
Expanded Wall Thickness, minimum	1.1 mm 0.043 in

Material Specifications

Material Type	Fiber-reinforced multi-layer sealing sleeve
----------------------	---

Environmental Specifications

Environmental Space

Aerial | Buried | Ducted

Packaging and Weights

Packaging quantity

1

Packaging Type

Bag | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

