



WRSS wraparound auxiliary heat shrink sleeve kit, cables with 0.60 to 3.00 inches cable diameter, 12 inches long

- Accommodates a wide range of pressure and temperature, ideal for hostile environments
- Designed to be used for diameter transitions in cable where a large shrink ratio is required
- Minimized total required splice length allowing installation on existing cables in confined areas

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

|                              |                           |
|------------------------------|---------------------------|
| <b>Regional Availability</b> | North America             |
| <b>Product Type</b>          | Heat shrink repair sleeve |
| <b>Product Series</b>        | WRSS                      |

## General Specifications

|                     |                  |
|---------------------|------------------|
| <b>Color</b>        | Black            |
| <b>Sealant Type</b> | Hotmelt adhesive |

## Dimensions

|   |                    |
|---|--------------------|
| <b>Length</b>                             | 304.8 mm   12 in   |
| <b>Expanded Inside Diameter, minimum</b>  | 300 mm   11.811 in |
| <b>Recovered Inside Diameter, maximum</b> | 60 mm   2.362 in   |
| <b>Single Cable Diameter, maximum</b>     | 76.2 mm   3 in     |
| <b>Single Cable Diameter, minimum</b>     | 15.24 mm   0.6 in  |

## Material Specifications

|                      |                     |
|----------------------|---------------------|
| <b>Material Type</b> | SuperSleeve sealing |
|----------------------|---------------------|

## Environmental Specifications

|                            |                 |
|----------------------------|-----------------|
| <b>Environmental Space</b> | Aerial   Buried |
|----------------------------|-----------------|

### Packaging and Weights

|                           |              |
|---------------------------|--------------|
| <b>Packaging quantity</b> | 1            |
| <b>Packaging Type</b>     | Bag   Carton |

### Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

