

BHD-12S



Double Block Hanger for 1/2 in coaxial cable (FSJ4) - Hardware Sold Separately (search 243095-SERIES-HARDWARE for options available)

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	Double block hanger
Mounting	Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod

Dimensions

Maximum Stack Height	4
Height	40.1 mm 1.579 in
Width	33 mm 1.299 in
Length	67.1 mm 2.642 in
Compatible Cable Diameter Range	13.5–15.5 mm
Compatible Diameter, maximum	15.5 mm 0.61 in
Compatible Diameter, minimum	13.5 mm 0.531 in
Nominal Size	1/2 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

BHD-12S

Material Type Engineered plastic

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 3.8 cm | 1.496 in

Width, packed 17.8 cm | 7.008 in

Length, packed 25.4 cm | 10 in

Packaging quantity 10

Weight, gross 0.37 kg | 0.816 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power