

# BHD-78

---



## Double Block Hanger for 7/8 in coaxial cable

### Product Classification

<b>Product Type</b>	Hanger kit
<b>Ordering Note</b>	CommScope® standard product (Global)

### General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Double block hanger
<b>Mounting</b>	3/8 in (M10) drilled cable ladder

### Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	42.9 mm   1.689 in
<b>Width</b>	40.1 mm   1.579 in
<b>Length</b>	80 mm   3.15 in
<b>Compatible Cable Diameter Range</b>	27.7–28.2 mm
<b>Compatible Diameter, maximum</b>	28.2 mm   1.11 in
<b>Compatible Diameter, minimum</b>	27.7 mm   1.091 in
<b>Nominal Size</b>	7/8 in

### Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

### Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

# BHD-78

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Environmental Strength Capability</b>	Double cable weight
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

<b>Height, packed</b>	5.1 cm   2.008 in
<b>Width, packed</b>	17.8 cm   7.008 in
<b>Length, packed</b>	22.9 cm   9.016 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.56 kg   1.235 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power