

# CK1834-000 | FAST-GGND-0078-CN01

---



FAST Weatherproofing Gel Sealed Grounding Transition Boot, ground line on 7/8 inch Feeder

- Gel-sealed weatherproofing boots for sealing coaxial cable connection points providing an efficient moisture block
- Wraparound design eliminates the need to disconnect the connectors before installation
- No tape, no mastics or tools required for installation and removal

## Product Classification

<b>Regional Availability</b>	Asia
<b>Product Type</b>	Weatherproofing boot
<b>Product Series</b>	FAST

## General Specifications

<b>Application</b>	Ground line on 7/8" Feeder
<b>Color</b>	Black

## Dimensions

<b>Length</b>	55 mm   2.165 in
<b>Cable Diameter for Seal, maximum</b>	29 mm   1.142 in
<b>Cable Diameter for Seal, minimum</b>	27 mm   1.063 in
<b>Inner Diameter</b>	32 mm   1.26 in

## Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Weatherproofing Method</b>	IP68

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

# CK1834-000 | FAST-GGND-0078-CN01

---

**Agency**

CHINA-ROHS  
REACH-SVHC  
ROHS

**Classification**

Below maximum concentration value  
Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)  
Compliant

