

CSG78-06B1A



SureGround® Universal Compact Grounding Kit for 7/8 in corrugated and smoothwall coaxial cable

Product Classification

Product Type	Grounding kit
Product Brand	SureGround®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Bonding Conductor Jacketing Material	PVC
Bonding Conductor Material	Copper
Bonding Conductor Wire Size	6 gauge
Cable Type	Corrugated Smoothwall
Color	Black
Grounding Kit Type	Compact SureGround® Grounding Kits
Grounding Strap Material	Tinned copper
Harmonized System (HS) Code	85366910 (Coaxial cable and other coaxial electric conductors)
Lug Attachment	Factory attached
Lug Type	One-hole lug
Thread Size	3/8 in

Dimensions

Enclosure Width	40.64 mm 1.6 in
Bonding Conductor Length	609.6 mm 24 in
Enclosure Length	63.5 mm 2.5 in
Compatible Diameter, maximum	28.372 mm 1.117 in
Compatible Diameter, minimum	27.559 mm 1.085 in
Nominal Size	7/8 in

CSG78-06B1A

Electrical Specifications

Current Handling	Tested to withstand 100,000 amps peak current surge
Current Handling Test Method	MIL-STD-1757
Grounding, Bonding and Shielding Test Method	MIL-STD-188-124A
Lightning Protection Test Method	IEC 1024-1

Material Specifications

Locking Bail Material	Stainless steel
Rivet Material	Tinned copper

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Blowing Rain Test Method	MIL-STD-810, Method 506
Corrosion Test Method	MIL-STD-1344, Method 1001
Freezing Rain/Icing Test Method	MIL-STD-810, Method 521
Humidity Test Method	MIL-STD-1344, Method 1002
Immersion Test Method	IEC 60529:2001, IP68
UV Resistance Test Method	MIL-STD-810, Method 505
Vibration Test Method	MIL-STD-202, Method 214
Weatherproofing Method	Tinned copper strap contact overmolded with EPDM rubber

Packaging and Weights

Height, packed	447.04 mm 17.6 in
Width, packed	396.24 mm 15.6 in
Length, packed	68.58 mm 2.7 in
Included	Grounding kit Hardware Lug
Packaging quantity	1
Weight, gross	0.36 kg 0.794 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

CSG78-06B1A

REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Grounding, Bonding and Shielding Test Method	Military Standard for Grounding, Bonding, and Shielding: Bond Resistance Requirement of a Maximum dc resistance of 0.001 ohm
Lightning Protection Test Method	Protection Against Lightning Electromagnetic Impulse, Table 1—Protection Level III–IV, 1995-02