760248052 | L-048-LN-5K-M12AQ/14D/GY/C



Fiber indoor cable, Single Jacket All-Dielectric, Gel-Free, 48 fibers, Stranded Microsheath Tube, Multimode OM4, Meters jacket marking, Agua jacket color, Cca Flame rating. Provides Rodent Resistance

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series L-LN

General Specifications

Cable Type Stranded microsheath tube

Non-armored **Construction Type**

Subunit Type Gel-free

Jacket Color Aqua

Jacket Marking Meters

Jacket Marking Method Inkjet

Jacket Marking Text COMMSCOPE GB F.O. CABLE 760248052 48X 50

/125 OM4 EN50575 CLASS C LSZH [SERIAL NUMBER] [METRE MARK]

Subunit, quantity

Fibers per Subunit, quantity 12

Total Fiber Count 48

Dimensions


Buffer Tube/Subunit Diameter 1.4 mm | 0.055 in 6.6 mm | 0.26 in

Diameter Over Jacket

Representative Image



760248052 | L-048-LN-5K-M12AQ/14D/GY/C



Material Specifications

Inner Jacket Material Low Smoke Zero Halogen (LSZH)

Mechanical Specifications

Minimum Bend Radius, loaded 130 mm | 5.118 in

Minimum Bend Radius, unloaded 90 mm | 3.543 in

Tensile Load, long term, maximum 850 N | 191.088 lbf

Tensile Load, short term, maximum 1450 N | 325.973 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Impact 2 N-m | 17.701 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Vertical Rise, maximum 1600 m | 5,249.344 ft

Optical Specifications

Fiber Type OM4, LazrSPEED®

COMMSCOPE®

760248052 | L-048-LN-5K-M12AQ/14D/GY/C

Environmental Specifications

Installation temperature 0 °C to +50 °C (+32 °F to +122 °F)

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards IEC 60794-1-2

EN50575 CPR Cable EuroClass Fire PerformanceCcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH)

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Temperature Cycle -10 °C to +60 °C (+14 °F to +140 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 46.6 kg/km | 31.314 lb/kft

Included Products

CS-5K-LT – LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

