

HFTP-AM

Customer Premise Wall Outlet

FEATURES AND BENEFITS

- Compact design (105x85x25mm)
- 4 cable ports (3-7mm), 2 at the bottom left, 1 top right, 1 back entrance
- Housing up to 2 fusion splices
- Adapter with shutter and laser warning logo on the applicable MID's
- Splicing to factory terminated pigtails
- Customer connection point has available space to allocate a second pigtail with connector and adapter
- Possibility to splice cable to cable
- Small lid to hide the screw preventing re-entering

KIT CONTENTS

- 4x tie-wraps (2mmx80mm)
- Foam band (80mmx15mm)
- 2x wall screws (5mm) and 2x wall plugs (5mm) (wall installment)
- 3 grommets (3-7mm)
- Stainless steel M4 nut and screw (Installed)
- Small lid
- 1 Pigtail/Adapter on the applicable MID's
- Installation instruction measurement tool with every 100 connectors
- Two dry cleaning wipes with each connector



The HFTP-AM wall outlet is a point of termination of the optical connection cable in a residential environment.

In its tray it allows to accommodate two fusion splices and store their corresponding fibers. The wall plug has two lower entrances, one upper and one rear for the connection cable.

The wall plug can be supplied without a cord or connector to be used as a transition box for an external or internal connection cable. Made of self-extinguishing ABS UL V-0 and stainless-steel screw and nut.

Specifications

Dimensions	
105 x 83 x 25mm (L x W x H)	
Cable Ports	
Number of Ports	Cable O.D. Range
4	3-7 mm
Capacity	
Splicing Capacity	2 fusion splices
Patching Capacity	2 SC adapters



HFTP - AM- XX X X - E

Connector Type

S1	SC/UPC
S2	SC/APC
NN	None for cable splicing
L1	LC/UPC
L2	LC/APC
LN	No pigtails and adapters but with LC Shutters

Number of Pigtails

0	No pigtails
1	1 pigtail
2	2 pigtails

Number of Adapters

0	No adapters
1	1 adapter
2	2 adapters

commscope.com

Visit our website or contact your local CommScope representative for more information. For technical assistance, customer service.

© 2021 CommScope, Inc. All rights reserved.

Unless otherwise noted, all trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope, Inc. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services. CommScope is committed to the highest standards of business integrity and environmental sustainability with a number of CommScope's facilities across the globe certified in accordance with international standards, including ISO 9001, TL 9000, and ISO 14001.

Further information regarding CommScope's commitment can be found at www.commscope.com/About-Us/Corporate-Responsibility-and-Sustainability.

PA-115593-EN (04/21)