

2-599175-2 | C-024-LA-5K-M12AQ/28G/GRP/E

Fiber Optic Cable, 24-fiber, OM4, aqua. Provides Rodent Resistance.

OBSOLETE

This product was discontinued on: March 31, 2023

Product Classification

| | |
|------------------------------|-------------------------------------|
| Regional Availability | Asia Australia/New Zealand EMEA |
| Portfolio | CommScope® |
| Product Type | Fiber indoor/outdoor cable |
| Product Series | C-LA |

General Specifications

| | |
|--------------------------|-------------------|
| Armor Type | Non-metallic rods |
| Cable Type | Loose tube |
| Filler, quantity | 2 |
| Jacket Color | Yellow |
| Jacket Marking | Meters |
| Subunit Type | Gel-filled |
| Total Fiber Count | 24 |

Dimensions

| | |
|-----------------------------|----------------------|
| Cable Length | 2000 m 6,561.68 ft |
| Diameter Over Jacket | 15 mm 0.591 in |

Mechanical Specifications

| | |
|--|------------------------|
| Minimum Bend Radius, loaded | 465 mm 18.307 in |
| Minimum Bend Radius, unloaded | 350 mm 13.78 in |
| Tensile Load, long term, maximum | 6000 N 1,348.854 lbf |
| Tensile Load, short term, maximum | 9000 N 2,023.281 lbf |

Optical Specifications

| | |
|-------------------|---------------------|
| Fiber Type | OM4, LazrSPEED® 550 |
|-------------------|---------------------|

2-599175-2 | C-024-LA-5K-M12AQ/28G/GRP/E

Optical Specifications, Wavelength Specific

| | |
|-----------------------------|---|
| Attenuation, maximum | 0.35 dB/km @ 1,300 nm 0.35 dB/km @ 1,550 nm 0.45 dB/km @ 1,310 nm |
| Standards Compliance | IEC 60794-1 TIA-492AAAD (OM4) |

Environmental Specifications

| | |
|---------------------------------|--|
| Installation temperature | -5 °C to +50 °C (+23 °F to +122 °F) |
| Operating Temperature | -25 °C to +70 °C (-13 °F to +158 °F) |
| Storage Temperature | -20 °C to +70 °C (-4 °F to +158 °F) |
| Environmental Space | Universal Low Smoke Zero Halogen (ULSZH) |

Packaging and Weights

| | |
|---------------------|----------------------------|
| Cable weight | 236 kg/km 158.585 lb/kft |
|---------------------|----------------------------|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable