

# SSH-158-3

---



SnapStak® Hanger for 1-5/8 in coaxial cable, triple stack capability, includes reinforcement bar

## Product Classification

|                      |                                      |
|----------------------|--------------------------------------|
| <b>Product Type</b>  | Hanger kit                           |
| <b>Product Brand</b> | SnapStak®                            |
| <b>Ordering Note</b> | CommScope® standard product (Global) |

## General Specifications

|                          |                             |
|--------------------------|-----------------------------|
| <b>Cables per Hanger</b> | 1                           |
| <b>Color</b>             | Silver                      |
| <b>Hanger Type</b>       | Snap-in hanger              |
| <b>Mounting</b>          | 3/4 in drilled cable ladder |

## Dimensions

|  |                    |
|--|--------------------|
| <b>Maximum Stack Height</b>            | 3                  |
| <b>Height</b>                          | 40.9 mm   1.61 in  |
| <b>Width</b>                           | 50.8 mm   2 in     |
| <b>Length</b>                          | 89.9 mm   3.539 in |
| <b>Compatible Cable Diameter Range</b> | 49–51.1 mm         |
| <b>Compatible Diameter, maximum</b>    | 51.1 mm   2.012 in |
| <b>Compatible Diameter, minimum</b>    | 49 mm   1.929 in   |
| <b>Nominal Size</b>                    | 1-5/8 in           |

## Electrical Specifications

|                                    |        |
|------------------------------------|--------|
| <b>Return Loss Effect, maximum</b> | 0.1 dB |
| <b>DTF Effect, maximum</b>         | 0.1 dB |

## Material Specifications

|                      |                 |
|----------------------|-----------------|
| <b>Material Type</b> | Stainless steel |
|----------------------|-----------------|

## Mechanical Specifications

# SSH-158-3

---

## Vibration Survival

≥4 hours at resonant frequency

## Environmental Specifications

### Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

### Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

### Environmental Strength Capability

Double cable weight

## Packaging and Weights

### Height, packed

22 cm | 8.661 in

### Width, packed

15 cm | 5.906 in

### Length, packed

14.4 cm | 5.669 in

### Packaging quantity

10

### Weight, gross

0.6 kg | 1.323 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power