# 760252032 | 0-004-CA-5Y-M04BK/28G/093



Fiber OSP cable, PE, Gel-filled Central Tube, CST, 4 fiber, Multimode OM3, Meters jacket marking, Black jacket color

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand

Portfolio CommScope®
Product Type Fiber OSP cable

Product Series O-CA

## General Specifications

**Cable Type** Central loose tube

Construction Type Armored
Subunit Type Gel-filled
Jacket Color Black
Jacket Marking Feet
Fibers per Subunit, quantity 4
Total Fiber Count 4

#### **Dimensions**

Buffer Tube/Subunit Diameter2.8 mm | 0.11 inDiameter Over Jacket9.1 mm | 0.358 in

## Mechanical Specifications

Minimum Bend Radius, loaded182 mm | 7.165 inMinimum Bend Radius, unloaded91 mm | 3.583 inTensile Load, long term, maximum890 N | 200.08 lbfTensile Load, short term, maximum2700 N | 606.984 lbfCompression20 N/mm | 114.203 lb/in

**Compression Test Method** IEC 60794-1-2 E3



## 760252032 | 0-004-CA-5Y-M04BK/28G/093

Flex 25 cycles

**Strain** See long and short term tensile loads

Strain Test Method IEC 60794-1-2-E1

Optical Specifications

**Fiber Type** OM3

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

**Environmental Specifications** 

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

Environmental Space Buried | Ducted | Outdoor

Water Penetration 24 h

**Water Penetration Test Method** IEC 60794-1 F5B

**Environmental Test Specifications** 

**Temperature Cycle**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Temperature Cycle Test Method** IEC 60794-1-2 F1

Packaging and Weights

Cable weight 92 kg/km | 61.821 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



\* Footnotes



# 760252032 | 0-004-CA-5Y-M04BK/28G/093

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

