


SWH-200-100



PIM Free, SnapWrap Cable Management Strap. Bundle multiple cable types and sizes into a 1/2" (12.7mm) to 2" (50.8mm) bundle with Snap-in installation. Package of 100

- Manage multiple cables in a single universal wrapping strap
- Replaces hangers and endless combinations of multi-cable grommets
- Simpler BOMs, easier standardization
- Optimized to reduce PIM while maximizing structural integrity

OBSOLETE

This product was discontinued on: January 9, 2024

Replaced By:

SWH-200-10

PIM Free, SnapWrap Cable Management Strap. Bundle multiple cable types and sizes into a 1/2" (12.7 mm) to 2" (50.8mm) bundle with Snap-in installation. Package of 10

Product Classification

Product Type	Cable management
Product Brand	PIM-Guard
Ordering Note	CommScope® standard product (Global)

General Specifications

Accessories	Hangers
Color	Black
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder
Patent Number	For patents see www.cs-pat.com

Dimensions

Maximum Stack Height	0
Height	34.8 mm 1.37 in
Width	34.8 mm 1.37 in
Length	228.6 mm 9 in
Compatible Cable Diameter Range	12.7–50.8 mm

SWH-200-100

Compatible Diameter, maximum	50.8 mm 2 in
Compatible Diameter, minimum	12.7 mm 0.5 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
Wind Speed, survival with 1/2 in (12 mm) radial ice	201.168 km/h 125 mph

Environmental Specifications

Installation temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	20 cm 7.874 in
Width, packed	51 cm 20.079 in
Length, packed	61 cm 24.016 in
Packaging quantity	100
Weight, gross	0.73 kg 1.609 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power