760252635 | C-006-DS-8M-MSUBL



Fiber indoor/outdoor cable, LSZH Riser Distribution, 6 fiber single-unit, Singlemode G.652.D, Meters jacket marking, Blue jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-DS

General Specifications

Cable Type Tight buffer

Jacket Color Blue

Jacket Marking Meters | Meters

Strength Members E-glass yarns

Total Fiber Count 6

Dimensions

Diameter Over Jacket 4.8 mm | 0.189 in

Material Specifications

Jacket MaterialLow Smoke Zero Halogen (LSZH)Inner Jacket MaterialLow Smoke Zero Halogen (LSZH)

Mechanical Specifications

Minimum Bend Radius, loaded 96 mm | 3.78 in

Minimum Bend Radius, unloaded 48 mm | 1.89 in

Tensile Load, short term, maximum 600 N | 134.885 lbf

Compression 5 N/mm | 28.551 lb/in

Compression Test Method IEC 60794-1-21 E3

Impact 1 N-m | 8.851 in lb

Impact Test Method IEC 60794-1-21 E4

Strain Test Method IEC 60794-1-21 E1



760252635 | C-006-DS-8M-MSUBL

Twist 10 cycles

Twist Test Method IEC 60794-1-21 E7

Optical Specifications

Fiber Type G.652.D | OS2

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.3 dB/km @ 1,550 nm | 0.40 dB/km @ 1,310 nm

Environmental Specifications

Installation temperature 0 °C to +50 °C (+32 °F to +122 °F)

Operating Temperature -10 °C to +70 °C (+14 °F to +158 °F)

Storage Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-3-24

Water Penentration 24 h

Water Penentration Test Method IEC 60794-1 F5C

Environmental Test Specifications

Temperature Cycle Test Method IEC 60794-1-22 F1

Packaging and Weights

Cable weight 22 kg/km | 14.783 lb/kft

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

