

# MLOC4-F1BXXM-5M



HELIAX® M-LOC Multiport cluster 4 ports SureFlex® cable assembly with interface type M-LOC latching male to Nex10 male, size 1/4", length 5 meters, covered by conduit shield

## Product Classification

<b>Product Type</b>	HELIAX® MLOC cluster, SureFlex® Premium, static PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	MLOC

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Attachment, Connector B</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	M-LOC Male
<b>Interface, Connector B</b>	NEX10 Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	5 m   16.404 ft
<b>Nominal Size</b>	1/4 in

## Electrical Specifications

<b>3rd Order IMD Static</b>	-119 dBm
<b>3rd Order IMD Static Test Method</b>	Two +43 dBm carriers

## VSWR/Return Loss

Frequency Band	Gated VSWR	Gated Return Loss (dB)	Insertion Loss, typical (dB)
1000–3000 MHz	1.07	30	1.89
3000–4200 MHz	1.11	26	2.28
4200–5000 MHz	1.12	25	2.51

# MLOC4-F1BXXM-5M

---

## Mechanical Specifications

**Minimum Bend Radius, multiple Bends** 25.4 mm | 1 in

**Minimum Bend Radius, single Bend** 25.4 mm | 1 in

## Environmental Specifications

**Installation temperature** -40 °C to +60 °C (-40 °F to +140 °F)

**Operating Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

**Storage Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

**Weatherproofing Method** HELIAX® SureGuard weatherproofing boot

## Included Products

- FSJ1-50A – FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket