760252639 | C-006-DS-5X-MSUBL



Fiber indoor/outdoor cable, LSZH Riser Distribution, 6 fiber single-unit, Multimode OM4 bend insensitive, Meters jacket marking, Blue jacket color

Product Classification

Regional Availability Asia | Australia/New Zealand

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-DS

General Specifications

Cable TypeTight buffer

Jacket Color Blue

Jacket Marking Meters | Meters

Strength Members E-glass yarns

Total Fiber Count 6

Dimensions

Diameter Over Jacket 4.8 mm | 0.189 in

Material Specifications

Jacket MaterialLow Smoke Zero Halogen (LSZH)Inner Jacket MaterialLow Smoke Zero Halogen (LSZH)

Mechanical Specifications

Minimum Bend Radius, loaded96 mm3.78 inMinimum Bend Radius, unloaded48 mm1.89 in

Tensile Load, short term, maximum 600 N | 134.885 lbf

Compression 5 N/mm | 28.551 lb/in

Compression Test Method IEC 60794-1-21 E3

Impact 1 N-m | 8.851 in lb

Impact Test Method IEC 60794-1-21 E4

Strain Test Method IEC 60794-1-21 E1

COMMSCOPE®

760252639 | C-006-DS-5X-MSUBL

Twist 10 cycles

Twist Test Method IEC 60794-1-21 E7

Optical Specifications

Fiber Type OM4, bend insensitive

Optical Specifications, Wavelength Specific

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Environmental Specifications

Installation temperature 0 °C to +50 °C (+32 °F to +122 °F)

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +158 \,^{\circ}\text{F)}$

Storage Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-3-24

Water Penentration 24 h

Water Penentration Test Method IEC 60794-1 F5C

Environmental Test Specifications

Temperature Cycle Test Method IEC 60794-1-22 F1

Packaging and Weights

Cable weight 22 kg/km | 14.783 lb/kft

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

