CS67Z3 BLU C7A 4/22 S/FTP RL 1KM



Product Classification

Regional Availability EMEA

Portfolio NETCONNECT®

Product Type Twisted pair cable

General Specifications

ANSI/TIA Category 7A

Cable Component Type Horizontal

Cable Type S/FTP (shielded)

Conductor Type, singlesSolidConductors, quantity8Jacket ColorBlue

Pairs, quantity 4

Transmission Standards ANSI/TIA-568.2-D | IEC 61156-7 | ISO/IEC 11801 Class FA

Dimensions

Cable Length 1,000 m | 3,280.84 ft

 Diameter Over Insulated Conductor
 1.501 mm | 0.059 in

 Diameter Over Jacket, nominal
 7.798 mm | 0.307 in


 Jacket Thickness
 0.635 mm | 0.025 in

Conductor Gauge, singles 22 AWG

Cross Section Drawing



1499101-4



Electrical Specifications

Characteristic Impedance100 ohmCoupling AttenuationType I

dc Resistance Unbalance, maximum 2 %

dc Resistance, maximum 6.51 ohms/100 m | 1.984 ohms/100 ft

Delay Skew, maximum 12 ns

Mutual Capacitance at Frequency 4.1 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 80 %

Operating Frequency, maximum 1200 MHz

Operating Voltage, maximum 80 V Safety Voltage Rating 240 V

Segregation Class d

1499101-4

Electrical Cable Performance

CS CommScope

STD Refers to the standard value listed under Transmission Standards in the Electrical Specifications above

TYP Typical Electrical Performance

IL Insertion Loss (dB/100m) NEXT Near End Crosstalk (dB/100m)

 ACR
 Attenuation to Crosstalk Ratio (dB/100m)
 PSNEXT
 Power Sum Near End Crosstalk (db/100m)

 PSACR
 Power Sum Attenuation to Crosstalk Ratio (dB/100m)
 ACRF
 Attenuation to Crosstalk Ratio - Far End (dB/100m)

PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m) RL Return Loss (dB)

TCL Transverse Conversion Loss (dB/100m) ELTCTL Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL TYP	ACR TYP	PSNEXT		PSACRF	RL	
			STD	TYP	STD	STD	TYP
4	3.5	90	82	90	79	23	35
10	5.4	88	82	90	71	25	40
16	6.8	86	82	90	67	25	40
20	7.6	85	82	90	65	25	40
31.25	9.6	83	82	90	61	25	40
62.5	14	79	82	90	55	25	40
100	18	76	82	90	51	23	40
125	20	73	82	90	49	22	38
200	25	68	82	90	45	21	35
250	27	66	82	90	43	20	35
300	30	63	82	90	41	20	30
600	43	45	75	85	35	20	27
800	49	37	75	83	32	19	25
1,000	57	29	75	83	31	18	25
1,200	63	22	75	82	29	17	22

Material Specifications

Conductor Material Bare copper

Insulation Material Foamed polyethylene (FPE)

Jacket Material Low Smoke Fire Retardant Zero Halogen (LSFRZH)

Shield (Tape) Material Aluminum/Polyester

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature $0 \,^{\circ}\text{C}$ to +50 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +122 $^{\circ}\text{F}$)

Operating Temperature $-20 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Acid Gas Test Method IEC 60754-2

Page 3 of 4



1499101-4

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings2EN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Fire Retardant Low Smoke Zero Halogen (FRLSZH)

Flame Test Method EN 50399 | IEC 60332-3

Smoke Test Method IEC 61034-2

Packaging and Weights

Cable weight 62.994 kg/km | 42.33 lb/kft

Packaging Type Reel