

Fiber Indoor/Outdoor Drop Cable, FTTH, 2 fibers, Singlemode, G.657.A2, Gel-free, Meters jacket marking, Yellow jacket color, Dca Flame Rating

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber drop cable
<b>Product Series</b>	L-DN


## General Specifications

<b>Cable Type</b>	Drop   Semi-tight buffer
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-free
<b>Jacket Color</b>	Yellow
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB OPTICAL CABLE 810009885/DB 2xG657A2 SM LSZH EN50575 CLASS D (Serial NUMBER) (METRE MARK)
<b>Subunit, quantity</b>	2
<b>Fibers per Subunit, quantity</b>	1
<b>Total Fiber Count</b>	2

## Dimensions

<b>Cable Length</b>	2,000 m   6,561.68 ft
<b>Buffer Tube/Subunit Diameter</b>	0.9 mm   0.035 in
<b>Diameter Over Jacket</b>	4 mm   0.157 in

## Representative Image



## Material Specifications

**Jacket Material** Low Smoke Zero Halogen (LSZH)

## Mechanical Specifications

**Minimum Bend Radius, unloaded** 60 mm | 2.362 in

**Tensile Load, long term, maximum** 600 N | 134.885 lbf

**Tensile Load, short term, maximum** 1200 N | 269.771 lbf

**Compression** 20 N/mm | 114.203 lb/in

**Compression Test Method** IEC 60794-1 E3

**Impact** 5 N-m | 44.254 in lb

**Impact Test Method** IEC 60794-1 E4

**Strain Test Method** IEC 60794-1 E1

**Twist** 5 cycles

**Twist Test Method** IEC 60794-1 E7

## Optical Specifications

**Fiber Type** G.657.A2, TeraSPEED®

## Environmental Specifications

**Installation temperature** -30 °C to +60 °C (-22 °F to +140 °F)

**Operating Temperature** -30 °C to +60 °C (-22 °F to +140 °F)

<b>Storage Temperature</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Cable Qualification Standards</b>	IEC 60794-1-2
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Dca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s1a
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d0
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Environmental Space</b>	Drop   Ducted   Façade   Indoor/Outdoor   UV resistant for outdoor and Low Smoke Zero Halogen
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F5

## Environmental Test Specifications

<b>Temperature Cycle</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1-2 F1

## Packaging and Weights

<b>Cable weight</b>	20 kg/km   13.439 lb/kft
---------------------	--------------------------

## Included Products

CS-8G-TB	-	Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)
----------	---	--

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable