

# FFV4S4-65B-R7-V2



20-port sector antenna, 4x 617-894, 8x 1695-2690 MHz 65° HPBW and 8x 3300-4000 MHz, Beamformer, 7x RET

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Cluster connectors for the beam-forming array, including eight RF ports plus one calibration port
- Beamforming array for 3300-4000 MHz, n77 and n78

## General Specifications

<b>Antenna Type</b>	Sector- and beamforming
<b>Band</b>	Multiband
<b>Calibration Connector Interface</b>	M-LOC
<b>Calibration Connector Quantity</b>	1
<b>Color</b>	Light Gray (RAL 7035)
<b>Grounding Type</b>	RF connector inner conductor and body grounded to reflector and mounting bracket
<b>Performance Note</b>	Outdoor usage
<b>Radome Material</b>	Fiberglass, UV resistant
<b>Reflector Material</b>	Aluminum
<b>RF Connector Interface</b>	4.3-10 Female   M-LOC
<b>RF Connector Location</b>	Bottom
<b>RF Connector Quantity, high band</b>	8
<b>RF Connector Quantity, mid band</b>	8
<b>RF Connector Quantity, low band</b>	4
<b>RF Connector Quantity, total</b>	20

## Remote Electrical Tilt (RET) Information

<b>RET Hardware</b>	CommRET v2
<b>RET Interface</b>	8-pin DIN Female   8-pin DIN Male
<b>RET Interface, quantity</b>	1 female   1 male
<b>Input Voltage</b>	10–30 Vdc
<b>Internal RET</b>	High band (1)   Low band (2)   Mid band (4)
<b>Power Consumption, active state, maximum</b>	8 W
<b>Power Consumption, idle state, maximum</b>	1 W

# FFV4S4-65B-R7-V2

**Protocol** 3GPP/AISG 2.0 (Single RET)

## Dimensions

**Width** 498 mm | 19.606 in


**Depth** 197 mm | 7.756 in

**Length** 2000 mm | 78.74 in

**Net Weight, antenna only** 38 kg | 83.776 lb

**TDD Column Spacing** 41 mm | 1.614 in

## Array Layout



Array ID	Frequency (MHz)	RF Connector	RET (SRET)	AISG No.	AISG RET UID
R1	617-894	1 - 2	1	AISG1	CPxxxxxxxxxxxxxxxxR1
R2	617-894	3 - 4	2	AISG1	CPxxxxxxxxxxxxxxxxR2
Y1	1695-2690	5 - 6	3	AISG1	CPxxxxxxxxxxxxxxxxY1
Y2	1695-2690	7 - 8	4	AISG1	CPxxxxxxxxxxxxxxxxY2
Y3	1695-2690	9 - 10	5	AISG1	CPxxxxxxxxxxxxxxxxY3
Y4	1695-2690	11 - 12	6	AISG1	CPxxxxxxxxxxxxxxxxY4
P1	3300-4000	13 - 20	7	AISG1	CPxxxxxxxxxxxxxxxxP1

(Sizes of colored boxes are not true depictions of array sizes)

## Port Configuration

# FFV4S4-65B-R7-V2



## Electrical Specifications

<b>Impedance</b>	50 ohm
<b>Operating Frequency Band</b>	1695 – 2690 MHz   3300 – 4000 MHz   617 – 894 MHz
<b>Polarization</b>	±45°
<b>Total Input Power, maximum</b>	1,400 W @ 50 °C

## Electrical Specifications

	R1,R2	R1,R2	Y1,Y3	Y1,Y3	Y1,Y3	Y1,Y3	Y2,Y4
<b>Frequency Band, MHz</b>	<b>617–698</b>	<b>698–894</b>	<b>1695–1880</b>	<b>1850–1990</b>	<b>1920–2200</b>	<b>2490–2690</b>	<b>1695–1880</b>
<b>RF Port</b>	1,2,3,4	1,2,3,4	5,6,9,10	5,6,9,10	5,6,9,10	5,6,9,10	7,8,11,12
<b>Gain, dBi</b>	13.8	14.8	15.9	16.3	16.5	17	15.8
<b>Beamwidth, Horizontal, degrees</b>	68	59	72	72	70	56	63
<b>Beamwidth, Vertical, degrees</b>	13.8	11.7	7.7	7.3	6.9	5.7	8.1
<b>Beam Tilt, degrees</b>	2–14	2–14	2–12	2–12	2–12	2–12	2–12
<b>USLS (First Lobe), dB</b>	17	16	17	19	18	19	16
<b>Front-to-Back Ratio at 180°, dB</b>	28	29	33	32	31	26	34
<b>Isolation, Cross Polarization, dB</b>	25	25	25	25	25	25	25

# FFV4S4-65B-R7-V2

Isolation, Inter-band, dB	25	25	25	25	25	25	25
VSWR   Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	250	250	200	200	200	200	200

## Electrical Specifications, BASTA

Frequency Band, MHz	617-698	698-894	1695-1880	1850-1990	1920-2200	2490-2690	1695-1880
Gain by all Beam Tilts, average, dBi	13.4	14.3	15.3	15.9	16.1	16.6	15.2
Gain by all Beam Tilts Tolerance, dB	±0.7	±0.6	±1	±0.4	±0.4	±0.5	±0.9
Beamwidth, Horizontal Tolerance, degrees	±5	±5	±7	±4	±4	±5	±4
Beamwidth, Vertical Tolerance, degrees	±0.8	±1.4	±0.6	±0.3	±0.5	±0.4	±0.5
USLS, beampeak to 20° above beampeak, dB		16	13	15	15	14	13
Front-to-Back Total Power at 180° ± 30°, dB	21	22	24	27	25	20	25
CPR at Boresight, dB	16	16	16	17	17	19	18
CPR at Sector, dB	9	7	9	8	6	4	7

## Electrical Specifications

	Y2,Y4	Y2,Y4	Y2,Y4	P1	P1
Frequency Band, MHz	1850-1990	1920-2200	2490-2690	3300-3800	3700-4000
RF Port	7,8,11,12	7,8,11,12	7,8,11,12	13-20	13-20
Gain, dBi	16.1	16.5	16.7	15.8	16.1
Beamwidth, Horizontal, degrees	64	60	59	88	82
Beamwidth, Vertical, degrees	7.7	7.3	6.1	6.2	5.8
Beam Tilt, degrees	2-12	2-12	2-12	0-10	0-10
USLS (First Lobe), dB	18	17	18	14	14
Front-to-Back Ratio at 180°, dB	37	37	30	31	30
Coupling level, Amp, Antenna port to Cal port, dB				26	26
Coupling level, max Amp Δ, Antenna port to Cal port, dB				±2	±2

# FFV4S4-65B-R7-V2

Coupler, max Amp $\Delta$ , Antenna port to Cal port, dB				0.9	0.9
Coupler, max Phase $\Delta$ , Antenna port to Cal port, degrees				7	7
Isolation, Cross Polarization, dB	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25
Isolation, Co-polarization, dB				19	19
VSWR   Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-140	-140
Input Power per Port at 50°C, maximum, watts	200	200	200	75	75

## Electrical Specifications, BASTA

Frequency Band, MHz	1850–1990	1920–2200	2490–2690	3300–3800	3700–4000
Gain by all Beam Tilts, average, dBi	15.8	16.2	16.3	15.2	15.5
Gain by all Beam Tilts Tolerance, dB	±0.4	±0.5	±0.5	±0.7	±0.5
Beamwidth, Horizontal Tolerance, degrees	±3	±6	±7	±17	±13
Beamwidth, Vertical Tolerance, degrees	±0.3	±0.6	±0.3	±0.4	±0.5
USLS, beampeak to 20° above beampeak, dB	15	16	13	13	12
Front-to-Back Total Power at 180° ± 30°, dB	28	29	25	23	23
CPR at Boresight, dB	21	21	18	16	16
CPR at Sector, dB	7	9	5	6	6

## Electrical Specifications, Broadcast 65°

Frequency Band, MHz	3300–3800	3700–4000
Gain, dBi	17.5	18
Beamwidth, Horizontal, degrees	65	65
Beamwidth, Vertical, degrees	6.3	5.9
Front-to-Back Total Power at 180° ± 30°, dB	27	27
USLS (First Lobe), dB	18	19

# FFV4S4-65B-R7-V2

## Electrical Specifications, Service Beam

	<b>3300-3800</b>	<b>3700-4000</b>
<b>Frequency Band, MHz</b>		
<b>Steered 0° Gain, dBi</b>	20.5	20.7
<b>Steered 0° Beamwidth, Horizontal, degrees</b>	25	25
<b>Steered 0° Front-to-Back Total Power at 180° ± 30°, dB</b>	30	30
<b>Steered 0° Horizontal Sidelobe, dB</b>	14	14
<b>Steered 30° Gain, dBi</b>	19.6	20.2
<b>Steered 30° Beamwidth, Horizontal, degrees</b>	28	25
<b>Steered 30° Front-to-Back Total Power at 180° ± 30°, dB</b>	29	28

## Electrical Specifications, Soft Split

	<b>3300-3800</b>	<b>3700-4000</b>
<b>Frequency Band, MHz</b>		
<b>Gain, dBi</b>	19.5	19.9
<b>Beamwidth, Horizontal, degrees</b>	32	29
<b>Front-to-Back Total Power at 180° ± 30°, dB</b>	29	29
<b>Horizontal Sidelobe, dB</b>	21	20

## Mechanical Specifications

<b>Wind Loading @ Velocity, frontal</b>	680.0 N @ 150 km/h (152.9 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, lateral</b>	178.0 N @ 150 km/h (40.0 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, maximum</b>	904.0 N @ 150 km/h (203.2 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, rear</b>	468.0 N @ 150 km/h (105.2 lbf @ 150 km/h)
<b>Wind Speed, maximum</b>	241 km/h (150 mph)

## Packaging and Weights

<b>Width, packed</b>	565 mm   22.244 in
<b>Depth, packed</b>	309 mm   12.165 in
<b>Length, packed</b>	2187 mm   86.102 in
<b>Weight, gross</b>	49.1 kg   108.247 lb

# FFV4S4-65B-R7-V2

---

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

## Included Products

BSAMNT-2F


– Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

## \* Footnotes

**Performance Note**

Severe environmental conditions may degrade optimum performance

# BSAMNT-2F



Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

## Product Classification

**Product Type** Fixed tilt mounting kit

## General Specifications

**Application** Outdoor

**Color** Silver

## Dimensions

**Compatible Diameter, maximum** 115 mm | 4.528 in

**Compatible Diameter, minimum** 60 mm | 2.362 in

**Weight, net** 3.8 kg | 8.378 lb

## Material Specifications

**Material Type** Galvanized steel

## Packaging and Weights

**Included** Brackets | Hardware

**Packaging quantity** 1

**Weight, gross** 4 kg | 8.818 lb

## Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



# BSAMNT-2F

---

