


# NG4-CMDKOR6



NG4access® Cabled Module, singlemode LC/UPC to stub, 576 fiber, Rollable Ribbon, indoor/outdoor

- Cabled modules enable the routing of fiber cable to the frame, where multiple connectors are terminated to the frame with a single click
- Integrated connectors ensure the cables are kept in sequential order, and help prevent accidental fiber breakage or disruption to adjacent fibers during installation
- Available in a pigtail version for splicing on frame or preterminated to 24-fiber microcable or conventional IFC cable

## Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cabled module
Product Brand	NG4access®
Product Series	NG4
Ordering Note	For fiber modules with custom cable lengths, please contact your local CommScope representative

## General Specifications

Configuration Type	NG4 Module to Stub tail
Adapters, quantity, front	576
Adapters, quantity, rear	1
Body Style	Straight orientation
Cable Color	Yellow
Cable Type	Indoor/outdoor - Rollable Ribbon
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	LC/UPC
Interface, rear	Stub tail
Polarity	Pairs, straight
Total Fibers, quantity	576

## Dimensions

# NG4-CMDKOR6

Height	13.3 mm   0.524 in
Width	159.9 mm   6.295 in
Depth	101 mm   3.976 in

## Ordering Tree

NG4 - CMD

Cabled module connector type #1

Singlemode	
K	LC ultra polish
M	LC angled polish

Far end connector type #2\*

Singlemode	
0	No connector/stub end

Cable type

	Number of Fibers	Outer Diameter	
R3	144	10.5 mm	.41"
R4	288	12.5 mm	.49"
R5	432	15.5 mm	.61"
R6	576	17.0 mm	.67"
R8	864	19.5 mm	.77"

Standard cable length\*\*\*

016	16 m (50')
023	23 m (75')
031	31 m (100')
046	46 m (150')
061	61 m (200')
092	92 m (300')
122	122 m (400')
138	138 m (450')
153	153 m (500')
183	183 m (600')
305	305 m (1000')

\*\*\*Use XXX for non-standard lengths in meters

76" breakout on LC end

## Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2

## Environmental Specifications

Operating Temperature	-5 °C to +40 °C (+23 °F to +104 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 85%, non-condensing

## Packaging and Weights

Packaging quantity	1
--------------------	---