Base Product



Fiber Optic Cable, Drop, Outdoor Arid Core Gel-Filled Tubes, Dielectric

- Fiber drop cables are typically used between the fiber terminal and the building or home and available for various indoor or outdoor applications
- Fiber drop cables are engineered to withstand the most demanding environmental conditions, including sun, heat, cold, moisture and heavy RF interference
- Superior mechanical and optical performance with unmatched stability and quality

Product Classification


| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America | |
|------------------------|---|--|
| Portfolio | CommScope® | |
| Product Type | Fiber drop cable | |
| Product Series | O-DN | |
| General Specifications | | |
| Cable Type | Central loose tube | |
| Construction Type | Non-armored | |
| Jacket Color | Black | |
| | | |

Ordering Tree

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 29, 2024



O-DN



Material Specifications

Jacket Material

ΡE

Mechanical Specifications

| Compression Test Method | FOTP-41 IEC 60794-1 E3 |
|-------------------------|---------------------------------------|
| Flex Test Method | FOTP-104 IEC 60794-1 E6 |
| Impact Test Method | FOTP-25 IEC 60794-1 E4 |
| Strain | See long and short term tensile loads |
| Strain Test Method | FOTP-33 IEC 60794-1 E1 |
| Twist Test Method | FOTP-85 IEC 60794-1 E7 |

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 29, 2024



O-DN

Environmental Specifications

| Installation temperature | -30 °C to +70 °C (-22 °F to +158 °F) |
|--------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Storage Temperature | -40 °C to +75 °C (-40 °F to +167 °F) |
| Cable Qualification Standards | ANSI/ICEA S-110-717 |
| Environmental Space | Aerial, lashed Buried |
| Jacket UV Resistance | UV stabilized |
| Water Penetration | 24 h |
| Water Penentration Test Method | FOTP-82 IEC 60794-1 F5 |

Environmental Test Specifications

| Cable Freeze | -2 °C 28.4 °F |
|-------------------------------|--------------------------------------|
| Cable Freeze Test Method | FOTP-98 IEC 60794-1 F15 |
| Drip | 70 °C 158 °F |
| Drip Test Method | FOTP-81 IEC 60794-1 E14 |
| Heat Age | -40 °C to +85 °C (-40 °F to +185 °F) |
| Heat Age Test Method | IEC 60794-1 F9 |
| Low High Bend | -30 °C to +60 °C (-22 °F to +140 °F) |
| Low High Bend Test Method | FOTP-37 IEC 60794-1 E11 |
| Temperature Cycle | -40 °C to +70 °C (-40 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3 IEC 60794-1 F1 |

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 29, 2024

