



Fiber OSP cable, LightScope ZWP® Mini Single Jacket All-Dielectric, Singlemode G.657.A1, 72 fiber Arid Core construction, Gel-filled, stranded loose tube, Meters jacket marking, Black jacket color

## Product Classification

|                              |                 |
|------------------------------|-----------------|
| <b>Regional Availability</b> | EMEA            |
| <b>Portfolio</b>             | CommScope®      |
| <b>Product Type</b>          | Fiber OSP cable |
| <b>Product Series</b>        | O-LN            |

## General Specifications

|                                     |  |
|-------------------------------------|--|
| <b>Cable Type</b>                   | Stranded loose tube  |
| <b>Construction Type</b>            | Non-armored  |
| <b>Subunit Type</b>                 | Gel-filled   |
| <b>Jacket Color</b>                 | Black  |
| <b>Jacket Marking</b>               | Meters   |
| <b>Jacket Marking Method</b>        | Inkjet   |
| <b>Jacket Marking Text</b>          | COMMSCOPE GB OPTICAL CABLE G657A1 SM 72 FIBER (SERIAL NUMBER) (MM/YYYY) (METER MARK) |
| <b>Subunit, quantity</b>            | 6  |
| <b>Fibers per Subunit, quantity</b> | 12   |
| <b>Total Fiber Count</b>            | 72   |

## Dimensions

|                                     |                   |
|-------------------------------------|-------------------|
| <b>Buffer Tube/Subunit Diameter</b> | 2 mm   0.079 in   |
| <b>Diameter Over Jacket</b>         | 9.5 mm   0.374 in |

## Representative Image



## Material Specifications

**Jacket Material** PE

## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 143 mm   5.63 in                      |
| <b>Minimum Bend Radius, unloaded</b>     | 95 mm   3.74 in                       |
| <b>Tensile Load, long term, maximum</b>  | 800 N   179.847 lbf                   |
| <b>Tensile Load, short term, maximum</b> | 2700 N   606.984 lbf                  |
| <b>Compression</b>                       | 22 N/mm   125.623 lb/in               |
| <b>Compression Test Method</b>           | IEC 60794-1 E3                        |
| <b>Flex</b>                              | 25 cycles                             |
| <b>Flex Test Method</b>                  | IEC 60794-1 E6                        |
| <b>Impact</b>                            | 2.94 N-m   26.021 in lb               |
| <b>Impact Test Method</b>                | IEC 60794-1 E4                        |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | IEC 60794-1 E1                        |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | IEC 60794-1 E7                        |
| <b>Vertical Rise, maximum</b>            | 1142 m   3,746.719 ft                 |

## Optical Specifications

**Fiber Type** G.657.A1

## Environmental Specifications

# 810010056/DB | O-072-LN-8F-M12NS/20G/BK

|                                      |  |
|--------------------------------------|--|
| <b>Installation temperature</b>      | -30 °C to +70 °C (-22 °F to +158 °F)           |
| <b>Operating Temperature</b>         | -40 °C to +70 °C (-40 °F to +158 °F)           |
| <b>Storage Temperature</b>           | -40 °C to +75 °C (-40 °F to +167 °F)           |
| <b>Cable Qualification Standards</b> | ANSI/ICEA S-87-640   EN 187105   IEC 60794-1-2 |
| <b>Environmental Space</b>           | Aerial, lashed   Buried                        |
| <b>Jacket UV Resistance</b>          | UV stabilized                                  |
| <b>Water Penetration</b>             | 24 h   |
| <b>Water Penetration Test Method</b> | IEC 60794-1 F5                                 |

## Environmental Test Specifications

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| <b>Cable Freeze</b>                  | -2 °C   28.4 °F                      |
| <b>Cable Freeze Test Method</b>      | IEC 60794-1 F15                      |
| <b>Drip</b>                          | 70 °C   158 °F                       |
| <b>Drip Test Method</b>              | IEC 60794-1 E14                      |
| <b>Heat Age</b>                      | -40 °C to +85 °C (-40 °F to +185 °F) |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                       |
| <b>Low High Bend</b>                 | -30 °C to +60 °C (-22 °F to +140 °F) |
| <b>Low High Bend Test Method</b>     | IEC 60794-1 E11                      |
| <b>Temperature Cycle</b>             | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | IEC 60794-1 F1                       |

## Packaging and Weights

|                     |                          |
|---------------------|--------------------------|
| <b>Cable weight</b> | 72 kg/km   48.382 lb/kft |
|---------------------|--------------------------|

## Included Products

|          |  |
|----------|--|
| CS-8F-TB | - Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber |
|----------|--|

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

# CS-8F-TB

---

Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber

## Product Classification

|                     |               |
|---------------------|---------------|
| <b>Portfolio</b>    | CommScope®    |
| <b>Product Type</b> | Optical fiber |

## General Specifications

|  |  |
|--|--|
| <b>Cladding Diameter</b>                             | 125 µm                                 |
| <b>Cladding Diameter Tolerance</b>                   | ±0.7 µm                                |
| <b>Cladding Non-Circularity, maximum</b>             | 0.7 %                                  |
| <b>Coating Diameter (Colored)</b>                    | 249 µm                                 |
| <b>Coating Diameter (Uncolored)</b>                  | 242 µm                                 |
| <b>Coating Diameter Tolerance (Colored)</b>          | ±13 µm                                 |
| <b>Coating Diameter Tolerance (Uncolored)</b>        | ±5 µm                                  |
| <b>Coating/Cladding Concentricity Error, maximum</b> | 12 µm                                  |
| <b>Core/Clad Offset, maximum</b>                     | 0.5 µm                                 |
| <b>Proof Test</b>                                    | 689.476 N/mm <sup>2</sup>   100000 psi |
| <b>Tight Buffer Diameter</b>                         | 900 µm                                 |
| <b>Tight Buffer Diameter Tolerance</b>               | ±40 µm                                 |

## Dimensions

|                            |                 |
|----------------------------|-----------------|
| <b>Fiber Curl, minimum</b> | 4 m   13.123 ft |
|----------------------------|-----------------|

## Mechanical Specifications

|   |   |
|---|---|
| <b>Macrobending, 20 mm Ø mandrel, 1 turn</b>    | 0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm |
| <b>Macrobending, 30 mm Ø mandrel, 10 turns</b>  | 0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm |
| <b>Macrobending, 50 mm Ø mandrel, 100 turns</b> | 0.03 dB @ 1,550 nm   0.05 dB @ 1,625 nm |
| <b>Coating Strip Force, maximum</b>             | 8.9 N   2.001 lbf                       |
| <b>Coating Strip Force, minimum</b>             | 1.3 N   0.292 lbf                       |
| <b>Dynamic Fatigue Parameter, minimum</b>       | 20                                      |

## Optical Specifications

|  |         |
|--|---------|
| <b>Cabled Cutoff Wavelength, maximum</b> | 1260 nm |
|--|---------|

# CS-8F-TB

---

|  |                    |
|--|--------------------|
| <b>Point Defects, maximum</b>              | 0.1 dB             |
| <b>Zero Dispersion Slope, maximum</b>      | 0.09 ps/[km-nm-nm] |
| <b>Zero Dispersion Wavelength, maximum</b> | 1324 nm            |
| <b>Zero Dispersion Wavelength, minimum</b> | 1300 nm            |

## Optical Specifications, Wavelength Specific

|  |   |
|--|---|
| <b>Attenuation, maximum</b>                                    | 0.50 dB/km @ 1,310 nm   0.50 dB/km @ 1,385 nm   0.50 dB/km @ 1,490 nm   0.50 dB/km @ 1,550 nm |
| <b>Dispersion, maximum</b>                                     | 18 ps(nm-km) at 1550 nm   3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm                    |
| <b>Index of Refraction</b>                                     | 1.467 @ 1,310 nm   1.467 @ 1,385 nm   1.468 @ 1,550 nm  |
| <b>Mode Field Diameter</b>                                     | 8.6 $\mu\text{m}$ @ 1,310 nm   9.8 $\mu\text{m}$ @ 1,550 nm                                   |
| <b>Mode Field Diameter Tolerance</b>                           | $\pm 0.4 \mu\text{m}$ @ 1310 nm   $\pm 0.5 \mu\text{m}$ @ 1550 nm                             |
| <b>Polarization Mode Dispersion Link Design Value, maximum</b> | 0.06 ps/sqrt(km)  |
| <b>Standards Compliance</b>                                    | ITU-T G.657.A1  |

## Environmental Specifications

|  |                    |
|--|--------------------|
| <b>Heat Aging, maximum</b>                   | 0.05 dB/km @ 85 °C |
| <b>Temperature Dependence, maximum</b>       | 0.05 dB/km         |
| <b>Temperature Humidity Cycling, maximum</b> | 0.05 dB/km         |
| <b>Water Immersion, maximum</b>              | 0.05 dB/km @ 23 °C |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## \* Footnotes

|  |   |
|--|---|
| <b>Temperature Dependence, maximum</b>       | Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)                                   |
| <b>Temperature Humidity Cycling, maximum</b> | Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity |