


860663466 | Radio Enclosure for Nokia AHLBBA and AHFIB and AHFIB



Middle of Pole Micro Concealment Enclosure for AHLBBA and AHFIB Nokia Radios

- Intended to be used with high powered remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures

Includes Standard Mounting kit for through bolt, clamp, and banding

Available After Market KIts, ordered separate:

-860649584S-xx 5" Standoff for wood poles

-860649584ST-xx Standoff for Round Tapered Poles

Product Classification

Product Type	Mid pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Fairfax Brown (SW 2856) Faux Concrete Federal Park Brown Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022) White (RAL 9010)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Power Supply Compatibility	CCI PSU-1200W-48-N
Radio Compatibility, Nokia	AHFIB AHLBBA
Radios Included	None

Dimensions

Height	1,117.6 mm 44 in
Width	533.4 mm 21 in
Depth	508 mm 20 in

860663466 | Radio Enclosure for Nokia AHLBBA and AHFIB

Electrical Specifications

Power/Fiber Input Trade size knockouts at rear side

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

Volume 0.303 m³ | 10.7 ft³

Weight (loaded) 136.078 kg | 300 lb

Weight (unloaded) 49.895 kg | 110 lb