

CLT4HM-6M-CO



MQ Multiport cluster 4 ports cable assembly with interface type MQ female to 4.3-10 male, size 1/4", length 6 meters

Product Classification

| | |
|-----------------------|--------------------------------------|
| Product Type | Wireless transmission cable assembly |
| Product Series | MQ |
| Warranty | Two years |

General Specifications

| | |
|---|------------------|
| Attachment, Connector A | Factory attached |
| Attachment, Connector B | Factory attached |
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | MQ Female |
| Interface, Connector B | 4.3-10 Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|-----------------|
| Length | 6 m 19.685 ft |
| Nominal Size | 1/4 in |

Port Configuration

| Pin Assignment | Label |
|----------------|-------------|
| 1 | MQ4-1 (R-) |
| 2 | MQ4-2 (CR-) |
| 3 | MQ4-3 (CL-) |
| 4 | MQ4-4 (L-) |

CLT4HM-6M-CO

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) | Insertion Loss, typical (dB) |
|----------------|-------|------------------|------------------------------|
| 0–2700 MHz | 1.151 | 23.1 | 2.4 |
| 2700–4200 MHz | 1.201 | 20.8 | 3 |
| 4200–6000 MHz | 1.36 | 16.5 | 4 |

Mechanical Specifications

| | |
|--|----------------|
| Minimum Bend Radius, multiple Bends | 25.4 mm 1 in |
| Minimum Bend Radius, single Bend | 25.4 mm 1 in |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +85 °C (-40 °F to +185 °F) |
| Immersion Test Method | IEC 60529, IP67 |

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |



* Footnotes

| | |
|-----------------|--|
| Warranty | For more information, please consult our Product Warranty guidelines |
|-----------------|--|