## UJXQPQXTF

#### **Base Product**



Ultra Low Loss (ULL) OM4 MPO8 (Non-Pinned) to MPO8 (Pinned), Fiber Trunk Cable Assembly, 24-Fiber, Dual Rated (OFNR/LSZH)

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Connector A, quantity 3

Color, boot A Gray

Color, connector A Aqua

Connector B, quantity 3

Color, boot B Gray
Color, connector B Aqua

Construction Type Stranded

Furcation Color Aqua

Interface, Connector A MPO-08/UPC Female

Interface, Connector B MPO-08/UPC Male

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 24

Dimensions

Breakout Length 22 in


Page 1 of 10

## UJXQPQXTF

Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

## Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

**Optical Specifications** 

Fiber Mode Multimode

**Fiber Type** OM4, LazrSPEED®

### **Environmental Specifications**

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



**COMMSCOPE®** 

# UJXQPQXTF

### Included Products

760248164 – Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 24 fiber multi-unit N-024-MP-5K-F08AQ/20T/D with 8 fiber 2.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color,

Dca flame rating

860659018 – MPO-08, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 2mm 860659024 – MPO-08, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 2mm



# 760248164 | N-024-MP-5K-F08AQ/20T/D



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 24 fiber multi-unit with 8 fiber 2.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color, Dca flame rating

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

Jacket Color Aqua

Jacket Marking Feet

Subunit, quantity 3

Fibers per Subunit, quantity 8

Total Fiber Count 24


**Dimensions** 

Buffer Tube/Subunit Diameter2 mm0.079 inDiameter Over Jacket7 mm0.276 in

Representative Image



# 760248164 | N-024-MP-5K-F08AQ/20T/D



### Mechanical Specifications

Minimum Bend Radius, loaded 105 mm | 4.134 in

Minimum Bend Radius, unloaded 70 mm | 2.756 in

**Tensile Load, long term, maximum** 200 N | 44.962 lbf

**Tensile Load, short term, maximum** 667 N | 149.948 lbf

**Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

FIEX Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 387 m | 1,269.685 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

### **Environmental Specifications**

Installation temperature  $0 \, ^{\circ}\text{C} \, \text{to} + 60 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 140 \, ^{\circ}\text{F})$ Operating Temperature  $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Storage Temperature  $-40 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ 

Page 5 of 10



# 760248164 | N-024-MP-5K-F08AQ/20T/D

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-4 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11Temperature Cycle $0 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $+32 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 43.3 kg/km | 29.096 lb/kft

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable





### MPO-08, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 2mm

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorAquaColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Male

Interface Feature Pinned

Total Fiber Count 8

**Dimensions** 

**Compatible Cable Diameter** 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

Fiber ModeMultimodeFiber TypeOM3 | OM4

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, ULL, maximum0.2 dBReturn Loss, minimum27 dB

Packaging and Weights



#### **Packaging quantity**

1

### Regulatory Compliance/Certifications

ication

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





### MPO-08, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 2mm

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorAquaColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Female

Interface Feature Unpinned

Total Fiber Count 8

**Dimensions** 

**Compatible Cable Diameter** 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

**Optical Specifications** 

Fiber ModeMultimodeFiber TypeOM3 | OM4

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

Packaging and Weights

**COMMSCOPE®** 

#### Packaging quantity

1

### Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliantUK-ROHSCompliant

