U3GQPQXTL

Base Product



Ultra Low Loss (ULL) Singlemode MPO8 (Non-Pinned) to MPO8 (Pinned), Fiber Trunk Cable Assembly, 96-Fiber, LZSH B2ca

Product Classification

Regional Availability Europe

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Connector A, quantity12Color, boot AGrayColor, connector AGreenConnector B, quantity12Color, boot BGray

Color, connector B Green

Construction Type Stranded

Furcation Color Yellow

 Interface, Connector A
 MPO-08/APC Female

 Interface, Connector B
 MPO-08/APC Male

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 96

Dimensions

Breakout Length 22 in


Page 1 of 10

U3GQPQXTL

Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

EN50575 CPR Cable EuroClass Fire Performance B2ca

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system





U3GQPQXTL

Included Products

760254320 – Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 96 fiber with 2.0 mm Subunits, N-096-MP-8G1-F08YL/20T/B2 Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

860659022 – MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm 860659028 – MPO-08, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 2mm



760254320 | N-096-MP-8G1-F08YL/20T/B2

96



Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 96 fiber with 2.0 mm Subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series N-MP

General Specifications

Cable TypeMPO trunk cableConstruction TypeNon-armoredSubunit TypeGel-freeJacket ColorYellowJacket MarkingFeetSubunit, quantity12Fibers per Subunit, quantity8

Dimensions

Total Fiber Count

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Jacket12.9 mm | 0.508 in

Mechanical Specifications

Minimum Bend Radius, loaded194 mm | 7.638 inMinimum Bend Radius, unloaded129 mm | 5.079 inTensile Load, long term, maximum200 N | 44.962 lbfTensile Load, short term, maximum667 N | 149.948 lbfCompression10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

760254320 | N-096-MP-8G1-F08YL/20T/B2

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 114 m | 374.016 ft

Optical Specifications

Fiber Type G.657.A2/B2

Environmental Specifications

Installation temperature0 °C to +60 °C (+32 °F to +140 °F)Operating Temperature0 °C to +70 °C (+32 °F to +158 °F)Storage Temperature-40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceB2caEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2

Environmental Test Specifications

 Low High Bend
 0 °C to +70 °C (+32 °F to +158 °F)

 Low High Bend Test Method
 FOTP-37 | IEC 60794-1 E11

 Temperature Cycle
 0 °C to +70 °C (+32 °F to +158 °F)

 Temperature Cycle Test Method
 FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 179.8 kg/km | 120.82 lb/kft

* Footnotes

760254320 | N-096-MP-8G1-F08YL/20T/B2

Operating Temperature Specification applicable to non-terminated bulk fiber cable



MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 TeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Male

Interface Feature Pinned

Total Fiber Count 8

Dimensions

Compatible Cable Diameter 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A2

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, ULL, typical0.35 dBReturn Loss, minimum65 dB

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSBelow maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





MPO-08, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 2mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandTeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Female

Interface Feature Unpinned

Total Fiber Count 8

Dimensions

Compatible Cable Diameter 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A2

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

Packaging and Weights

Packaging quantity

1

Classification

Regulatory Compliance/Certifications

Agency CHINA-ROHS Below maximum concentration value ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system **REACH-SVHC** Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant Compliant **UK-ROHS**

