

FGS-HNTS-F-12MM-A



FiberGuide® Top Support Adjustable C-Bracket Kit, 12mm for 4x12in System

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Support mounting kit
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Product Feature	Adjustable Height
Color	Black
Orientation	Horizontal
Section Type	Bracket

Dimensions

Height	304.8 mm 12 in
Width	41.148 mm 1.62 in
Length	384.048 mm 15.12 in
Thread Size	12 mm
System Dimensions	102 mm x 305 mm (4 in x 12 in)

Ordering Tree

FGS-HNTS-F-12MM-A

FGS - - - - - - -

For Section Size

9	empty	4 x 4 in, 4 x 6 in
	F	4 x 12 in

For Threaded Rod Size

10	1/2	1/2 in
	1/2-LP	1/2 in, low profile
	12MM	12 mm
	12MM-LP	12 mm, low profile
	14MM	14 mm
	14MM-LP	14 mm, low profile
	16MM	16 mm
	16MM-LP	16 mm, low profile
	5/8	5/8 in
	5/8-LP	5/8 in, low profile

11	A	Adjustable
----	---	------------

Material Specifications

Material Type Carbon steel

Packaging and Weights

Included Hardware

Packaging quantity 1

Weight, net 2.517 kg | 5.55 lb