

NOVUX™ Hardened Mulfi-fiber Terminal, 12 HMFOC ports, 2 fibers per port, Dielectric flat loose tube cable with HMFOC plug (female/no pin), 2000 ft/609 m

- NOVUX™ Hardened Multi-fiber Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX™ HMT terminals are well suited for fiber-rich applications and available with 12 or 24
   Fibers; no internal splitter option
- Available with flat dielectric up to 24 fiber or flat toneable/locatable up to 12 fiber. Terminals can be used as a distribution point within a network or as a final multifiber drop terminal where more than a single fiber is required to service an SFU or cellular tower
- NOVUX™ smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

#### **Product Classification**

Regional Availability

Asia | EMEA | Latin America | North America

Product Type Access terminal, without splitter/tap

 Product Brand
 NOVUX™

 Product Series
 HMT

Minimum Order Quantity

### General Specifications

Cable Type Dielectric - Flat - Loose Tube

Cable, quantity

**Distribution Type** 12 ports, 2 fibers per port

**Drop Port Type**Hardened multi-fiber (HMFOC) jack, male/pinned

Enclosure Color Black (RAL 9005)

Multi-fiber Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Multi-fiber Port, quantity 12

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

**COMMSCOPE®** 

Port, quantity 12

Stub Type Hardened multi-fiber (HMFOC) plug, female/no pin

**Dimensions** 


 Height
 80 mm | 3.15 in


 Width
 128 mm | 5.039 in

 Length
 207 mm | 8.15 in

 Cable Length, stub
 2000 ft (609 m)

### Dimension Drawing






### Port Configuration

NOVUXHT	TECHNOLOGIES AVAILABLE	SMALL	MEDIUM	LARGE
HMT Series	Multi-fiber	Up to 24f	Up to 24f	Up to 24f
		2 ports, each 2, 4, 6, 8 or 12f	6 ports, each 2, 3 or 4f	12 ports, each 2f
		3 ports, each 2, 4, 6, or 8f	8 ports 2 or 3f	
		4 ports, each 2, 4, or 6f		



### Ordering Tree



### Material Specifications

Enclosure Material Type Hardened plastic

Optical Specifications

**Fiber Type** G.657.A1/A2

**Operating Wavelength Range** 1260 – 1635 nm

**Attenuation Single Ports, maximum** 0.65 dB

Attenuation Cable Coefficient, maximum 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

Insertion Loss, Stub Connector, maximum0.65 dBReturn Loss, Connector, typical65 dB

#### **Environmental Specifications**

**Operating Temperature** -40 °C to +65 °C (-40 °F to +149 °F)

**Relative Humidity** 5%–100%, condensing

Environmental Space Above ground | Below ground

**Qualification Standards** IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

**UV Resistance** UV stabilized

Packaging and Weights

Packaging quantity

**COMMSCOPE®** 

**Packaging Type** Box | Universal spool, wood: terminal is on the top of the spool, stub deploys

#### Regulatory Compliance/Certifications

Classification CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system **REACH-SVHC** Compliant as per SVHC revision on www.commscope.com/ProductCompliance

**ROHS** Compliant **UK-ROHS** Compliant



**Agency**