



Fiber OSP cable, LightScope ZWP® Blown Single Jacket All-Dielectric, 12 fiber, Central Tube Construction, Singlemode G.657.A1, Gel-filled, Meters jacket marking, Black jacket color

Product Classification

Regional Availability	Europe
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	B-CN


General Specifications

Cable Type	Central tube, all dielectric Microcable
Construction Type	Non-armored
Subunit Type	Gel-filled
Filler, quantity	0
Inner Jacket Color	White
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMSCOPE GB OPTICAL CABLE BLW 810010120/DB 12x G657A1 SM HDPE [SERIAL NUMBER] [METER MARK]
Subunit, quantity	1
Fibers per Subunit, quantity	12
Total Fiber Count	12

Dimensions

Buffer Tube/Subunit Diameter	3 mm 0.118 in
Diameter Over Jacket	3.9 mm 0.154 in

Representative Image



Material Specifications

Jacket Material High density polyethylene (HDPE)

Mechanical Specifications

Minimum Bend Radius, loaded	47 mm 1.85 in
Minimum Bend Radius, storage coils	47 mm 1.85 in
Minimum Bend Radius, unloaded	47 mm 1.85 in
Tensile Load, long term, maximum	70 N 15.737 lbf
Compression	10 N/mm 57.101 lb/in
Compression Test Method	IEC 60794-1-21 E3
Flex	25 cycles
Impact	2 N-m 17.701 in lb
Impact Test Method	IEC 60794-1-21 E4
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1-21 E1
Twist	10 cycles
Twist Test Method	IEC 60794-1-21 E7

Optical Specifications

810010120/DB | B-012-CN-8F-M12BK/30G

Fiber Type G.657.A1

Environmental Specifications

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)
Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)
Storage Temperature -20 °C to +60 °C (-4 °F to +140 °F)
Cable Qualification Standards IEC 60794-1-2 | IEC 60794-5-10
Environmental Space Air-blown, microduct
Jacket UV Resistance UV stabilized
Water Penetration 24 h
Water Penetration Test Method IEC 60794-1 F5

Environmental Test Specifications

Low High Bend Test Method IEC 60794-1-21 E11
Temperature Cycle -20 °C to +60 °C (-4 °F to +140 °F)
Temperature Cycle Test Method IEC 60794-1-22 F1

Packaging and Weights

Cable weight 8.9 kg/km | 5.981 lb/kft

Included Products

CS-8F-LT – Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable