


# 810010033/DB | C-024-LN-8W-M12BK/25D/E



Fiber indoor/outdoor cable, LightScope® ZWP Single Jacket All-Dielectric, LSZH, 24 fiber, Gel-Free, Stranded Loose Tube, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color, Eca flame rating

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-LN

## General Specifications

<b>Cable Type</b>	Stranded loose tube
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-free
<b>Filler, quantity</b>	3
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB OPTICAL CABLE OS2 SM 24 FIBER EN50575 CLASS E [SERIAL NUMBER] [MM /YY] [METRE MARK]
<b>Subunit, quantity</b>	2
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	24

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	2.5 mm   0.098 in
<b>Diameter Over Jacket</b>	11.7 mm   0.461 in

## Representative Image



## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	175 mm   6.89 in
<b>Minimum Bend Radius, unloaded</b>	117 mm   4.606 in
<b>Tensile Load, long term, maximum</b>	800 N   179.847 lbf
<b>Tensile Load, short term, maximum</b>	2700 N   606.984 lbf
<b>Compression</b>	22 N/mm   125.623 lb/in
<b>Compression Test Method</b>	FOTP-41   IEC 60794-1 E3
<b>Flex</b>	25 cycles
<b>Flex Test Method</b>	FOTP-104   IEC 60794-1 E6
<b>Impact</b>	3 N-m   26.552 in lb
<b>Impact Test Method</b>	FOTP-25   IEC 60794-1 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	FOTP-33   IEC 60794-1 E1
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	FOTP-85   IEC 60794-1 E7
<b>Vertical Rise, maximum</b>	654 m   2,145.669 ft

## Optical Specifications

<b>Fiber Type</b>	G.652.D and G.657.A1
-------------------	----------------------

## Environmental Specifications

<b>Installation temperature</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

# 810010033/DB | C-024-LN-8W-M12BK/25D/E

<b>Storage Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Cable Qualification Standards</b>	ANSI/ICEA S-104-696   EN 187105   Telcordia GR-20   Telcordia GR-409
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Eca
<b>Environmental Space</b>	Aerial, lashed   Buried   Low Smoke Zero Halogen (LSZH)
<b>Flame Test Listing</b>	EN 50399
<b>Flame Test Method</b>	EN 50399   IEC 60332-1-2   IEC 60754-2
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	FOTP-82   IEC 60794-1 F5

## Environmental Test Specifications

<b>Cable Freeze</b>	-2 °C   28.4 °F
<b>Cable Freeze Test Method</b>	FOTP-98   IEC 60794-1 F15
<b>Drip</b>	70 °C   158 °F
<b>Drip Test Method</b>	FOTP-81   IEC 60794-1 E14
<b>Heat Age</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Heat Age Test Method</b>	IEC 60794-1 F9
<b>Low High Bend</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Low High Bend Test Method</b>	FOTP-37   IEC 60794-1 E11
<b>Temperature Cycle</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	FOTP-3   IEC 60794-1 F1

## Packaging and Weights

<b>Cable weight</b>	125 kg/km   83.996 lb/kft
---------------------	---------------------------

## Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber  
250um

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable