## ICX8200-24ZP | RUCKUS ICX 8200-24ZP





#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Ethernet switch

Product Brand RUCKUS®

### General Specifications

Layer 3 (STATIC, RIP, OSPF)

Switching Capacity, maximum 320 Gb/s

1 GbE RJ45 Ports, quantity, maximum
1 GbE SFP Ports, quantity, maximum
4
10 GbE SFP+ Ports, quantity, maximum
4

1/2.5 GbE RJ45 Ports, quantity, maximum 24 25 GbE SFP28 Ports, quantity, maximum 4

PoE Power Budget, maximum 740 W Switches per Stack, maximum 12

Aggregate Stack Bandwidth, maximum 1200 Gb/s

PoE/PoE+YesStackingYessFlowYes

OpenFlow with Hybrid Port Mode Yes

Campus Fabric Technology No

Redundant Power Option No

Hot Swap Internal Power Supplies & Fans No

**802.3bt2 (90 W PoE Power per Port)** No

**VRF** Yes

EEE (Energy Efficient Ethernet) Yes

IPsec VPN, with service module No

COMMSC PE®

Yes

# ICX8200-24ZP | RUCKUS ICX 8200-24ZP

MACsec	No
BGP	No
Reversible Airflow Option	No
VxLAN	Yes
Multi Chassis Trunking (MCT)	No

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

