ICX8200-24 | **RUCKUS ICX 8200-24**



Entry-Level+ Access 24 Ports 1G Switch

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

4

Yes

Product Type Ethernet switch

RUCKUS® Product Brand

General Specifications

OpenFlow with Hybrid Port Mode

248 Gb/s **Switching Capacity, maximum**

24 1 GbE RJ45 Ports, quantity, maximum 1 GbE SFP Ports, quantity, maximum 4 4 10 GbE SFP+ Ports, quantity, maximum

25 GbE SFP28 Ports, quantity, maximum

12 Switches per Stack, maximum

Aggregate Stack Bandwidth, maximum 1200 Gb/s

PoE/PoE+ No Stacking Yes sFlow Yes Layer 3 (STATIC, RIP, OSPF) Yes

Campus Fabric Technology No

Redundant Power Option No

Hot Swap Internal Power Supplies & Fans No

802.3bt2 (90 W PoE Power per Port) No

VRF Yes

EEE (Energy Efficient Ethernet) Yes

IPsec VPN, with service module No

MACsec No

BGP No

COMMSCOPE®

ICX8200-24 | RUCKUS ICX 8200-24

Reversible Airflow OptionNoVxLANYesMulti Chassis Trunking (MCT)No

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

