

HELIAX® Hanger Spacing Guidelines

Hanger Spacing

Recommended maximum hanger spacings based on 150 ft. (46 m) tower height assumption are tabulated below for various wind speed and ice conditions. The recommendations are based on guidelines stated in EIA Standard RS-222, wind tunnel and vibration tests. They are current as of December 2018 and supersede previous recommendations.

These guidelines assume that all hangers are properly installed and tightened.

Standard Tower Configuration Spacing: 3 to 4 ft. (0.9 to 1.2 m)

For Typical Climates: Use the 125 mph (200 km/h), 1/2 in (13 mm) ice conditions

Severe or Mild Climates: Use the wind speed and ice conditions that most closely approximate the expected worst case conditions for the local climate



1: Snap-in Hangers

Nominal Cable Size	Hanger Part Number	Recommended Maximum Hanger Spacing, feet (meters)					
Wind Speed:		85 mph (137 km/h)			100 mph (160 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
1/2 in	SSH-12	4 (1.2)	3 (0.9)	2 (0.6)	4 (1.2)	3 (0.9)	2 (0.6)
7/8 in	SSH-78	4 (1.2)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)
1-1/4 in	SSH-114	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)
1-5/8 in	SSH-158	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)
Wind Speed:		125 mph (200 km/h)			150 mph (240 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
1/2 in	SSH-12	3 (0.9)	3 (0.9)	2 (0.6)	3 (0.9)	2 (0.6)	1 (0.3)
7/8 in	SSH-78	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	1 (0.3)	1 (0.3)
1-1/4 in	SSH-114	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	1 (0.3)	1 (0.3)
1-5/8 in	SSH-158	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	1 (0.3)	1 (0.3)

Snap-in Hangers: Table 1

Definitions and Assumptions 1. Per EIA-222 Standard: Coefficient of drag for coaxial cable is 1.2 (cylindrical members). Ice forms completely around member (360 degrees). Combined wind and ice loading is reduced by 25% to reflect lower probability of wind and ice occurring simultaneously. 2. Wind speeds are maximum, which includes gust factors and exposure factors. 3. Hoisting grips are installed following manufacture guidelines and supporting the vertical load of the cable.



2: SnapStak® Plus Adjustable Hangers

Nominal Cable Size	Actual Cable Size	Hanger Part Number	Recommended Maximum Hanger Spacing, feet (meters)					
Wind Speed:			85 mph (137 km/h)			100 mph (160 km/h)		
Radial Ice:			No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
1/2 in	14mm - 25mm	SSH-M	4 (1.2)	3 (0.9)	2 (0.6)	4 (1.2)	3 (0.9)	2 (0.6)
1-5/8 in	36.1mm - 51mm	SSH-XL	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)
Wind Speed:			125 mph (200 km/h)			150 mph (240 km/h)		
Radial Ice:			No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
1/2 in	14mm - 25mm	SSH-M	3 (0.9)	3 (0.9)	2 (0.6)	3 (0.9)	2 (0.6)	1 (0.3)
1-5/8 in	36.1mm - 51mm	SSH-XL	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	1 (0.3)	1 (0.3)

SnapStak Plus Adjustable Hangers: Table 2



3: PIM Isolator for Snap-in and SnapStak® Plus Adjustable Hangers

* Spacing guidelines apply to isolator use with all stainless steel snap-in hangers from 1/2" nominal (SSH-12) to 51 mm (SSH-XL)

Part Number	Recommended Maximum Hanger Spacing, feet (meters)						
Wind Speed:		85 mph (137 km/h)			100 mph (160 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
SA-ISO		3 (0.9)	3 (0.9)	2 (0.6)	3 (0.9)	3 (0.9)	2 (0.6)
Part Number	Recommended Maximum Hanger Spacing, feet (meters)						
Wind Speed:		125 mph (200 km/h)			150 mph (240 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
SA-ISO		3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	2 (0.6)	1 (0.3)

PIM Isolator: Table 3

Definitions and Assumptions 1. Per EIA-222 Standard: Coefficient of drag for coaxial cable is 1.2 (cylindrical members). Ice forms completely around member (360 degrees). Combined wind and ice loading is reduced by 25% to reflect lower probability of wind and ice occurring simultaneously. 2. Wind speeds are maximum, which includes gust factors and exposure factors. 3. Hoisting grips are installed following manufacture guidelines and supporting the vertical load of the cable.

4: SnapTak PIM-Guard™ Adjustable Hangers



Nominal Cable Size	Actual Cable Size	Hanger Part Number	Recommended Maximum Hanger Spacing, feet (meters)					
Wind Speed:			85 mph (137 km/h)			100 mph (160 km/h)		
Radial Ice:			No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
1/2 in	4.0mm - 11.0mm	SSH-411	4 (1.2)	3 (0.9)	3 (0.9)	4 (1.2)	3 (0.9)	3 (0.9)
1/2 in	11.0mm - 17.0mm	SSH-1117	4 (1.2)	3 (0.9)	3 (0.9)	4 (1.2)	3 (0.9)	3 (0.9)
1/2 in	26.0mm - 30.0mm	SSH-2630	4 (1.2)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)
1/2 in	36.0mm - 42.0mm	SSH-3642	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)
Wind Speed:			125 mph (200 km/h)			150 mph (240 km/h)		
Radial Ice:			No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
1/2 in	4.0mm - 11.0mm	SSH-411	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	1 (0.3)
1/2 in	11.0mm - 17.0mm	SSH-1117	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	1 (0.3)
1/2 in	26.0mm - 30.0mm	SSH-2630	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	1 (0.3)	1 (0.3)
1/2 in	36.0mm - 42.0mm	SSH-3642	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	1 (0.3)	1 (0.3)

SnapTak Adjustable Hangers: Table 4

5: SnapWrap Cable Management Strap



Part Number	Recommended Maximum Hanger Spacing, feet (meters)					
Wind Speed:	85 mph (137 km/h)			100 mph (160 km/h)		
Radial Ice:	No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
	SWH-200-10	3 (0.9)	3 (0.9)	2 (0.6)	3 (0.9)	2 (0.6)
Part Number	Recommended Maximum Hanger Spacing, feet (meters)					
Wind Speed:	125 mph (200 km/h)			150 mph (240 km/h)		
Radial Ice:	No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
	SWH-200-10	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	1 (0.3)

SnapWrap: Table 5

Definitions and Assumptions 1. Per EIA-222 Standard: Coefficient of drag for coaxial cable is 1.2 (cylindrical members). Ice forms completely around member (360 degrees). Combined wind and ice loading is reduced by 25% to reflect lower probability of wind and ice occurring simultaneously. 2. Wind speeds are maximum, which includes gust factors and exposure factors. 3. Hoisting grips are installed following manufacture guidelines and supporting the vertical load of the cable.



6: Mini Click-On and Mini Block Hangers

NR - Not Recommended

Nominal Cable Size	Hanger Part Number	Recommended Maximum Hanger Spacing, feet (meters)					
		85 mph (137 km/h)			100 mph (160 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
6 mm - 8 mm	68MCLICK, BHD-14 , 1-2 Stack	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	2 (0.6)
6 mm - 8 mm	68MCLICK, BHD-14 , 3 Stack	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	1.5 (0.61)
9 mm - 12 mm	912MCLICK, BHD-38 , 1-2 Stack	4 (1.2)	4 (1.2)	3 (0.9)	4 (1.2)	3 (0.9)	3 (0.9)
9 mm - 12 mm	912MCLICK, BHD-38 , 3 Stack	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	2 (0.6)
13 mm - 16 mm	1316MCLICK, BHD-12S , 1 Stack	4 (1.2)	4 (1.2)	4 (1.2)	4 (1.2)	3 (0.9)	3 (0.9)
13 mm - 16 mm	1316MCLICK, BHD-12S , 2 Stack	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)
13 mm - 16 mm	1316MCLICK, BHD-12S , 3 Stack	3 (0.9)	3 (0.9)	2 (0.6)	3 (0.9)	2 (0.6)	2 (0.6)
Wind Speed:		125 mph (200 km/h)			150 mph (240 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
6 mm - 8 mm	68MCLICK, BHD-14 , 1 Stack	1.5 (0.46)	1.5 (0.46)	1.5 (0.46)	1.5 (0.46)	1.5 (0.46)	1.5 (0.46)
6 mm - 8 mm	68MCLICK, BHD-14 , 2 Stack	1.5 (0.46)	1.5 (0.46)	1.5 (0.46)	1.5 (0.46)	1 (0.3)	NR
6 mm - 8 mm	68MCLICK, BHD-14 , 3 Stack	1.5 (0.46)	1.5 (0.46)	1.5 (0.46)	NR	NR	NR
9 mm - 12 mm	912MCLICK, BHD-38 , 1-2 Stack	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	2 (0.6)
9 mm - 12 mm	912MCLICK, BHD-38 , 3 Stack	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)	1.5 (0.46)	1.5 (0.46)
13 mm - 16 mm	1316MCLICK, BHD-12S , 1-2 Stack	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	2 (0.6)
13 mm - 16 mm	1316MCLICK, BHD-12S , 3 Stack	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)	1.5 (0.46)	1 (0.3)

Mini Click-On and Mini Block Hangers: Table 6

Definitions and Assumptions 1. Per EIA-222 Standard: Coefficient of drag for coaxial cable is 1.2 (cylindrical members). Ice forms completely around member (360 degrees). Combined wind and ice loading is reduced by 25% to reflect lower probability of wind and ice occurring simultaneously. 2. Wind speeds are maximum, which includes gust factors and exposure factors. 3. Hoisting grips are installed following manufacture guidelines and supporting the vertical load of the cable.

7: Click-On and Block Hangers



Nominal Cable Size	Hanger Part Number	Recommended Maximum Hanger Spacing, feet (meters)					
		85 mph (137 km/h)			100 mph (160 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
1/2 in	L4CLICK , BHD-12 , SHK-12-*-P 1-4 Stack	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)
7/8 in	L5CLICKB , BHD-78 , SHK-78-*-P 1-4 Stack	4 (1.2)	4 (1.2)	4 (1.2)	3 (0.9)	3 (0.9)	3 (0.9)
1-1/4 in	L6CLICK , BHD-114 , SHK-114-1-P 1-2 Stack	4 (1.2)	4 (1.2)	4 (1.2)	3 (0.9)	3 (0.9)	3 (0.9)
1-1/4 in	L6CLICK , BHD-114 , 3-4 Stack	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)
1-5/8 in	L7CLICK , BHD-158 , SHK-158-1-P 1 Stack	4 (1.2)	4 (1.2)	4 (1.2)	3 (0.9)	3 (0.9)	3 (0.9)
1-5/8 in	L7CLICK , BHD-158 , 2-4 Stack	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)
Wind Speed:		125 mph (200 km/h)			150 mph (240 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
1/2 in	L4CLICK , BHD-12 , SHK-12-*-P 1-4 Stack	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	2 (0.6)
7/8 in	L5CLICKB , BHD-78 , SHK-78-*-P 1-2 Stack	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	2 (0.6)
7/8 in	L5CLICKB , BHD-78 , SHK-78-*-P 3-4 Stack	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)
1-1/4 in	L6CLICK , BHD-114 , SHK-114-1-P 1-2 Stack	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	2 (0.6)
1-1/4 in	L6CLICK , BHD-114 , 3-4 Stack	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)
1-5/8 in	L7CLICK , BHD-158 , SHK-158-1-P 1 Stack	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)	2 (0.6)	2 (0.6)
1-5/8 in	L7CLICK , BHD-158 , 2-4 Stack	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)	2 (0.6)

Click-On and Block Hangers: Table 7

* These hanger spacings have been specified based on using the Click-On and Block Hangers with CommScope specified hardware kits. Definitions and Assumptions 1. Per EIA-222 Standard: Coefficient of drag for coaxial cable is 1.2 (cylindrical members). Ice forms completely around member (360 degrees). Combined wind and ice loading is reduced by 25% to reflect lower probability of wind and ice occurring simultaneously. 2. Wind speeds are maximum, which includes gust factors and exposure factors. 3. Hoisting grips are installed following manufacture guidelines and supporting the vertical load of the cable.



8: Standard Hangers

Nominal Cable Size	Hanger Part Number	Recommended Maximum Hanger Spacing, feet (meters)					
		85 mph (137 km/h)			100 mph (160 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
1/2 in	43211A	4 (1.2)	3 (0.9)	2 (0.6)	4 (1.2)	3 (0.9)	2 (0.6)
5/8 in	42396A-9	5 (1.5)	5 (1.5)	4 (1.2)	5 (1.5)	5 (1.5)	4 (1.2)
7/8 in	42396A-5	5 (1.5)	5 (1.5)	4 (1.2)	5 (1.5)	5 (1.5)	4 (1.2)
1-1/4 in	42396A-1	4 (1.2)	4 (1.2)	4 (1.2)	4 (1.2)	4 (1.2)	3 (0.9)
1-5/8 in	42396A-2	4 (1.2)	4 (1.2)	4 (1.2)	4 (1.2)	3 (0.9)	3 (0.9)
3 in	31766A-11	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)
4 in	31766A-10	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)
5 in	33598-5	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)
Wind Speed:		125 mph (200 km/h)			150 mph (240 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
1/2 in	43211A	4 (1.2)	3 (0.9)	2 (0.6)	3 (0.9)	2 (0.6)	1 (0.3)
5/8 in	42396A-9	5 (1.5)	4 (1.2)	3 (0.9)	4 (1.2)	3 (0.9)	3 (0.9)
7/8 in	42396A-5	5 (1.5)	4 (1.2)	3 (0.9)	4 (1.2)	3 (0.9)	2 (0.6)
1-1/4 in	42396A-1	4 (1.2)	4 (1.2)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)
1-5/8 in	42396A-2	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	3 (0.9)	2 (0.6)
3 in	31766A-11	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)
4 in	31766A-10	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)
5 in	33598-5	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)	5 (1.5)

Standard Hangers: Table 8

Definitions and Assumptions 1. Per EIA-222 Standard: Coefficient of drag for coaxial cable is 1.2 (cylindrical members). Ice forms completely around member (360 degrees). Combined wind and ice loading is reduced by 25% to reflect lower probability of wind and ice occurring simultaneously. 2. Wind speeds are maximum, which includes gust factors and exposure factors. 3. Hoisting grips are installed following manufacture guidelines and supporting the vertical load of the cable.


9: Standard Hangers for Elliptical Waveguide



Nominal Cable Size	Hanger Part Number	Recommended Maximum Hanger Spacing, feet (meters)					
		85 mph (137 km/h)			100 mph (160 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
EW20	31766A-10	6 (1.8)	6 (1.8)	6 (1.8)	6 (1.8)	6 (1.8)	6 (1.8)
EW28	31766A-11	6 (1.8)	6 (1.8)	6 (1.8)	6 (1.8)	6 (1.8)	5.5 (1.68)
EW34, EWP34	42396A-15	6 (1.8)	6 (1.8)	6 (1.8)	6 (1.8)	5.5 (1.68)	6 (1.8)
EW43, EWP43	42396A-16	6 (1.8)	6 (1.8)	5.5 (1.68)	5 (1.5)	5 (1.5)	4.5 (1.37)
EW52, EWP52	42396A-8	5.5 (1.68)	5 (1.5)	4.5 (1.37)	4.5 (1.37)	4.5 (1.37)	4 (1.2)
EW63, EWP63	42396A-7	5 (1.5)	4.5 (1.37)	4 (1.2)	4 (1.2)	4 (1.2)	3.5 (1.07)
EW64, EWP64	42396A-1	5 (1.5)	6 (1.8)	4 (1.2)	4.5 (1.37)	4 (1.2)	3.5 (1.07)
EW77, EWP77	42396A-11	5 (1.5)	6 (1.8)	4 (1.2)	4.5 (1.37)	4 (1.2)	3.5 (1.07)
EW85	42396A-5	5.5 (1.68)	6 (1.8)	4 (1.2)	4.5 (1.37)	4 (1.2)	3.5 (1.07)
EW90, EWP90	42396A-5	5.5 (1.68)	6 (1.8)	4 (1.2)	4.5 (1.37)	4 (1.2)	3.5 (1.07)
EW127A, EWP127A	42396A-9	5.5 (1.68)	4.5 (1.37)	3.5 (1.07)	4.5 (1.37)	4 (1.2)	3 (0.9)
EW132, EWP132	42396A-9	5.5 (1.68)	4.5 (1.37)	3.5 (1.07)	4.5 (1.37)	4 (1.2)	3 (0.9)
EW180, EWP180	43211A	6 (1.8)	4.5 (1.37)	3.5 (1.07)	5 (1.5)	4 (1.2)	3 (0.9)
EW220, EW240	43211A	6 (1.8)	4.5 (1.37)	3.5 (1.07)	5 (1.5)	4 (1.2)	3 (0.9)
Wind Speed:		125 mph (200 km/h)			150 mph (240 km/h)		
Radial Ice:		No Ice	1/2 in (13 mm)	1 in (25 mm)	No Ice	1/2 in (13 mm)	1 in (25 mm)
EW20	31766A-10	5.5 (1.68)	5.5 (1.68)	5 (1.5)	4.5 (1.37)	4.5 (1.37)	4 (1.2)
EW28	31766A-11	5 (1.5)	5 (1.5)	4.5 (1.37)	4 (1.2)	4 (1.2)	3.5 (1.07)
EW34, EWP34	42396A-15	4.5 (1.37)	4.5 (1.37)	4 (1.2)	4 (1.2)	3.5 (1.07)	4 (1.2)
EW43, EWP43	42396A-16	4 (1.2)	4 (1.2)	3.5 (1.07)	3.5 (1.07)	3.5 (1.07)	3 (0.9)
EW52, EWP52	42396A-8	3.5 (1.07)	3.5 (1.07)	3 (0.9)	3 (0.9)	3 (0.9)	2.5 (0.76)
EW63, EWP63	42396A-7	3.5 (1.07)	3 (0.9)	2.5 (0.76)	2.5 (0.76)	2.5 (0.76)	2 (0.6)
EW64, EWP64	42396A-1	3.5 (1.07)	3 (0.9)	2.5 (0.76)	3 (0.9)	2.5 (0.76)	2 (0.6)
EW77, EWP77	42396A-11	3.5 (1.07)	3 (0.9)	2.5 (0.76)	3 (0.9)	2.5 (0.76)	2 (0.6)
EW85	42396A-5	3.5 (1.07)	3 (0.9)	2.5 (0.76)	3 (0.9)	2.5 (0.76)	2 (0.6)
EW90, EWP90	42396A-5	3.5 (1.07)	3 (0.9)	2.5 (0.76)	3 (0.9)	2.5 (0.76)	2 (0.6)
EW127A, EWP127A	42396A-9	3.5 (1.07)	3 (0.9)	2.5 (0.76)	3 (0.9)	2.5 (0.76)	2 (0.6)
EW132, EWP132	42396A-9	4 (1.2)	3 (0.9)	2.5 (0.76)	3 (0.9)	2.5 (0.76)	2 (0.6)
EW180, EWP180	43211A	4 (1.2)	3 (0.9)	2.5 (0.76)	3.5 (1.07)	2.5 (0.76)	2 (0.6)
EW220, EW240	43211A	4 (1.2)	3 (0.9)	2.5 (0.76)	3.5 (1.07)	2.5 (0.76)	2 (0.6)

Standard Hanger for Elliptical Waveguide: Table 9

Definitions and Assumptions 1. Per EIA-222 Standard: Coefficient of drag for coaxial cable is 1.2 (cylindrical members). Ice forms completely around member (360 degrees). Combined wind and ice loading is reduced by 25% to reflect lower probability of wind and ice occurring simultaneously. 2. Wind speeds are maximum, which includes gust factors and exposure factors. 3. Hoisting grips are installed following manufacture guidelines and supporting the vertical load of the cable.



10: KwikClamp™ Hangers (only available in Europe, the Middle East, and Africa)

Nominal Cable Size	Hanger Part Number	Recommended Maximum Hanger Spacing, feet (meters)
Wind Speed:		85 mph (137 km/h)
Radial Ice:		No Ice
1/4 in	F1-CLAMP , 1-4 Stack	6 (1.83)
1/2 in	F4-CLAMP , 1-4 Stack	6 (1.83)
4.5-9 mm	F-CLAMP-A , 1-4 Stack	6 (1.83)
4.5-9 mm	F-CLAMP-A2 , 1-3 Stack	6 (1.83)
7-9 mm / 22-34 mm	F-CLAMP-A2A2CC-4B , 4 Stack	6 (1.83)
7-9 mm / 22-34 mm	F-CLAMP-A2CC-4B , 4 Stack	6 (1.83)
7-22 mm	F-CLAMP-B , 1-3 Stack	6 (1.83)
7-22 mm	F-CLAMP-B2 , 2-3 Stack	6 (1.83)
22-34 mm	F-CLAMP-C , 1-3 Stack	6 (1.83)
34-46 mm	F-CLAMP-D , 1-3 Stack	6 (1.83)
9-12 mm	F-CLAMP-E , 1-4 Stack	6 (1.83)
9-12 mm	F-CLAMP-E2 , 1-3 Stack	6 (1.83)
1/2 in	L4-CLAMP , 1-4 Stack	6 (1.83)
7/8 in	L5-CLAMP , 1-4 Stack	6 (1.83)
1 1/4 in	L6-CLAMP , 1-4 Stack	6 (1.83)
1 5/8 in	L7-CLAMP , 1-3 Stack	6 (1.83)
3/8 in	R8-CLAMP , 1-4 Stack	6 (1.83)

Clamp Hanger Blocks: Table 7

Trademarks

All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of ANDREW an Amphenol Company. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to ANDREW products or services. ANDREW is committed to the highest standards of business integrity and environmental sustainability, with a number of ANDREW facilities across the globe certified in accordance with international standards, including ISO 9001, TL 9000, and ISO 14001.

These products are covered by one or more U.S. patents or their foreign equivalents. For patents, see www.adwpat.com

ANDREW an Amphenol company
2601 Telecom Parkway, Richardson, Texas, 75082, USA
www.andrew.com

Technical Support
+1 888 297 6433, Option 3 (Toll Free US and Canada)
awpnarsupport@andrew.com

Notice: ANDREW disclaims any liability or responsibility for the results of improper or unsafe installation, inspection, maintenance, or removal practices.
Aviso: ANDREW no acepta ninguna obligación ni responsabilidad como resultado de prácticas incorrectas o peligrosas de instalación, inspección, mantenimiento o retiro.
Avis: ANDREW décline toute responsabilité pour les conséquences de procédures d'installation, d'inspection, d'entretien ou de retrait incorrectes ou dangereuses.
Hinweis: ANDREW lehnt jede Haftung oder Verantwortung für Schäden ab, die aufgrund unsachgemäßer Installation, Überprüfung, Wartung oder Demontage auftreten.
Atenção: A ANDREW abdica do direito de toda responsabilidade pelos resultados de práticas inadequadas e sem segurança de instalação, inspeção, manutenção ou remoção.
Avvertenza: ANDREW declina eventualità responsabilità derivanti dall'esecuzione di procedure di installazione, ispezione, manutenzione e smontaggio improprie o poco sicure.
注意: ANDREW 公司申明對於不恰當或不安全的安裝、檢驗、維修或拆卸操作所導致的後果不負任何義務和責任

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners.