
760251972 | C-024-LA-5Y-M06BK/21G/093



Fiber indoor/outdoor cable, loose tube gel-filled CST, 24 fiber, Multimode OM3, Meters jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-LA

General Specifications

Armor Type Corrugated steel

Cable Type Stranded loose tube

Construction TypeArmoredSubunit TypeGel-filled

Filler, quantity 2

Jacket ColorBlackJacket MarkingMeters

Subunit, quantity 4

Fibers per Subunit, quantity 6

Total Fiber Count 24


Dimensions

Buffer Tube/Subunit Diameter2.1 mm | 0.083 inDiameter Over Jacket11.9 mm | 0.469 in

Representative Image



760251972 | C-024-LA-5Y-M06BK/21G/093



Mechanical Specifications

Minimum Bend Radius, loaded238 mm | 9.37 inMinimum Bend Radius, unloaded119 mm | 4.685 inTensile Load, short term, maximum2000 N | 449.618 lbfCompression15 N/mm | 85.652 lb/in

Compression Test Method IEC 60794-1-2 E3

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1-21 E1

Optical Specifications

Fiber Type OM3

Optical Specifications, Wavelength Specific

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Environmental Specifications

Installation temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Environmental Space Buried | Ducted | Indoor/Outdoor | Low Smoke Zero Halogen (LSZH)

Flame Test Method | IEC 60332-1 | IEC 60332-3-24 | IEC 60754-2 | IEC 61034-2

Water Penentration 24 h

Water Penentration Test Method IEC 60794-1 F5B

Page 2 of 3



760251972 | C-024-LA-5Y-M06BK/21G/093

Environmental Test Specifications

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method IEC 60794-1-2 F1

Packaging and Weights

Cable weight 164 kg/km | 110.203 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

