


# 2-599170-4 | C-008-CA-8W-M08YL/28G/GRP/D



Outdoor Fiber Optic Cable, 8-fiber, OS2, ULSZH, loose tube, gel-filled. Provides Rodent Resistance.

## OBSOLETE

This product was discontinued on: March 31, 2023

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-CA

## General Specifications

<b>Armor Type</b>	Non-metallic rods
<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-filled
<b>Filler, quantity</b>	1
<b>Jacket Color</b>	Yellow
<b>Jacket Marking</b>	Meters
<b>Fibers per Subunit, quantity</b>	8
<b>Total Fiber Count</b>	8

## Dimensions

<b>Cable Length</b>	2000 m   6,561.68 ft
<b>Diameter Over Jacket</b>	9 mm   0.354 in

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	228.6 mm   9 in
<b>Minimum Bend Radius, unloaded</b>	175.3 mm   6.902 in
<b>Tensile Load, long term, maximum</b>	750 N   168.607 lbf

# 2-599170-4 | C-008-CA-8W-M08YL/28G/GRP/D

**Tensile Load, short term, maximum** 2002 N | 450.068 lbf

## Optical Specifications

**Fiber Type** OS2

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.35 dB/km @ 1,300 nm | 0.35 dB/km @ 1,550 nm | 0.45 dB/km @ 1,310 nm

**Standards Compliance** IEC 60794-1 | TIA-492CAAB (OS2)

## Environmental Specifications

**Installation temperature** -5 °C to +50 °C (+23 °F to +122 °F)

**Operating Temperature** -20 °C to +70 °C (-4 °F to +158 °F)

**Storage Temperature** -20 °C to +70 °C (-4 °F to +158 °F)

**Environmental Space** Universal Low Smoke Zero Halogen (ULSZH)

## Packaging and Weights

**Cable weight** 94 kg/km | 63.165 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

CS-8W-LT – TeraSPEED® G652D/G657A1 Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable