

F4C-HMHM-7M-P-SGW



HELIAX® 1/2" Superflexible SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male with HELIAX® SureGuard weatherproofing, 7 m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

| | |
|-----------------------|-------------------------------|
| Product Type | SureFlex® Premium, static PIM |
| Product Brand | HELIAX® SureFlex® |
| Product Series | RSJ4-50 |

General Specifications

| | |
|---|------------------|
| Attachment, Connector A | Factory attached |
| Attachment, Connector B | Factory attached |
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | 4.3-10 Male |
| Interface, Connector B | 4.3-10 Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|-----------------|
| Length | 7 m 22.966 ft |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|---|----------------------|
| 3rd Order IMD Static | -119 dBm |
| 3rd Order IMD Static Test Method | Two +43 dBm carriers |
| DTF, Connector A | -34 dB |
| DTF, Connector B | -34 dB |

VSWR/Return Loss

F4C-HMHM-7M-P-SGW

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 698–960 MHz | 1.101 | 26.4 |
| 1700–2200 MHz | 1.101 | 26.4 |
| 2200–2700 MHz | 1.135 | 24 |
| 3400–3800 MHz | 1.222 | 20 |

Jumper Assembly Sample Label



Environmental Specifications

| | |
|-------------------------------|--|
| Immersion Test Method | Meets IEC 60529:2001, IP68 in mated condition |
| Weatherproofing Method | HELIAX [®] SureGuard weatherproofing boot |

Packaging and Weights

| | |
|-----------------|----------------------|
| Included | Weatherproofing boot |
|-----------------|----------------------|