

Fiber indoor/Outdoor OFNR/LSZH Riser Light Duty MPO Patchcord Cable with Rollable Ribbon

## Product Classification

**Regional Availability**

Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio**

CommScope®

**Product Type**

Fiber indoor/outdoor cable

**Product Series**

N-MP

## General Specifications

**Cable Type**

MPO trunk cable

**Construction Type**

Non-armored

**Subunit Type**

Gel-free

**Fibers per Ribbon, quantity**

12

**Jacket Color**

Black

**Jacket Marking**

Feet

**Total Fiber Count**


12

## Dimensions

**Diameter Over Jacket**

3 mm | 0.118 in

## Representative Image



## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 60 mm   2.362 in                      |
| <b>Minimum Bend Radius, unloaded</b>     | 24 mm   0.945 in                      |
| <b>Tensile Load, long term, maximum</b>  | 30 N   6.744 lbf                      |
| <b>Tensile Load, short term, maximum</b> | 100 N   22.481 lbf                    |
| <b>Compression</b>                       | 4 N/mm   22.841 lb/in                 |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 10 cycles                             |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 0.74 N-m   6.55 in lb                 |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |

## Optical Specifications

|                   |                           |
|-------------------|---------------------------|
| <b>Fiber Type</b> | G.657.A2/B2   G.657.A2/B2 |
|-------------------|---------------------------|

## Environmental Specifications

|                                 |                                      |
|---------------------------------|--------------------------------------|
| <b>Installation temperature</b> | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Operating Temperature</b>    | 0 °C to +70 °C (+32 °F to +158 °F)   |

# 760256410 | Z-012-MP-RR-F30BK/8G1/99K/C

|   |   |
|---|---|
| <b>Storage Temperature</b>                          | -40 °C to +70 °C (-40 °F to +158 °F)                                    |
| <b>Cable Qualification Standards</b>                | ANSI/ICEA S-83-596   Telcordia GR-409                                   |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | Cca   |
| <b>EN50575 CPR Cable EuroClass Smoke Rating</b>     | s1  |
| <b>EN50575 CPR Cable EuroClass Droplets Rating</b>  | d0  |
| <b>EN50575 CPR Cable EuroClass Acidity Rating</b>   | a1  |
| <b>Environmental Space</b>                          | Low Smoke Zero Halogen (LSZH)   Riser                                   |
| <b>Flame Test Listing</b>                           | NEC OFNR-ST1 (UL) and c(UL)   |
| <b>Flame Test Method</b>                            | CSA FT4   IEC 60332-1-2   IEC 60754-2   IEC 61034-2   UL 1666   UL 1685 |

## Environmental Test Specifications

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| <b>Heat Age</b>                      | 0 °C to +85 °C (+32 °F to +185 °F)   |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                       |
| <b>Low High Bend</b>                 | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11            |
| <b>Temperature Cycle</b>             | 0 °C to +70 °C (+32 °F to +158 °F)   |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1              |

## Packaging and Weights

|                     |                          |
|---------------------|--------------------------|
| <b>Cable weight</b> | 7.9 kg/km   5.309 lb/kft |
|---------------------|--------------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ANATEL        | Compliant  |
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## Included Products

|              |   |  |
|--------------|---|--|
| CS-8G1-RR-MP | – | Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Rollable Ribbon Fiber (ITU-T G.657.A2, B2) |
|--------------|---|--|

\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable